



Shockwave

Part No: TLS.01.1F11

Description:

Shockwave Wideband 5G/4G Direct Mount External Antenna With N Type(M) connector

Features:

Applicable for 5G/4G cellular bands

600-6000MHz Wideband Operational

Over 45% efficiency and 2.3 dBi gain

Mechanically robust for indoor/outdoor applications

Height: 79.45mm (3.13")

Diameter: 42mm(1.65")

IP67 Waterproof

N type(M) connector

RoHS & Reach Compliant



 Specifications Antenna Characteristics Radiation Patterns Mechanical Drawing 		
 3. Antenna Characteristics 4. Radiation Patterns 5. Mechanical Drawing 	1. Introduction	3
4. Radiation Patterns5. Mechanical Drawing	2. Specifications	4
5. Mechanical Drawing	3. Antenna Characteristics	6
	4. Radiation Patterns	8
6. Installation Guide	5. Mechanical Drawing	18
	6. Installation Guide	19
7. Packaging	7. Packaging	20
Changelog	Changelog	21

Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein. Reproduction, use or disclosure to third parties without express permission is strictly prohibited.













1. Introduction



The Shockwave TLS.01.1F11 is a permanent mount, waterproof, external 5G/4G cellular operating at the wideband 600- 6000MHz frequency with an N type male direct mount connector. It has been designed to be used on a Ground Plane. It can be used in mobile and fixed applications for 5G/4G wireless such as:

- Public safety
- HD Video Streaming
- Utilities and Smart Cities
- Fleet Management
- Agricultural
- Industrial

This antenna has superior performance over wide-bands compared to traditional whip antennas. Up to 90% efficiency and with a minimum 2.3dBi peak gain over all cellular bands result when mounted on a 30x30 cm ground plane. Stable radiation patterns over low angles provides consistent gain in the horizontal plane, meaning that it is especially suitable for cellular applications.

A unique indent tab on the base of the antenna allows a wrench to be used to solidly lock the antenna on top of its mounting location, where an N type female connector juts out from a metal panel. Waterproof Orings around the bottom base prevent water from leaking under the antenna.

The TLS.01 antenna is IP67 waterproof against short periods of immersion in water jets in commercial cleaning environments, which makes the antenna ideal for 5G/4G/3G/Cat M/NB-IoT applications either in indoor or in harsh outdoor environments. For more information contact your regional Taoglas customer support team.



2. Specifications

Electrical								
Band	Frequency (MHz)	Efficiency (%)	Average Gain (dB)	Peak Gain (dBi)	Impedance	Max Input Power	Polarization	Radiation Pattern
5GNR/4G Band 71	617~698	46.5	-3.2	-1				
4G/3G Band 12,13,14,17,28,29	698~806	95.2	-0.2	3.1				
4G/3G/NB-IoT/Cat M Band 5,8,18,19,20,26,27	824~960	84.5	-0.7	3.2				
5GNR/4G Band 21,32,74,75,76	1427~1518	71.9	-1.4	2.9				
4G/3G Band 1,2,3,4,9,23,25,35,39,66	1710~2200	65.5	-1.8	2.7	50 Ω	100W	Vertical	Omni-Directional
4G/3G Band 7,38,41	2490~2690	62.7	-2	3.4				
5GNR/4G Band 22,42,48,77,78	3300~3800	41.1	-4.1	2.5				
LTE5200/ Wi-Fi 5800	5150~5925	45.9	-3.4	5.3				

^{*}Measured on 30*30cm ground plane

ivieasured on 30 Social groun	Mechanical
Dimension (mm)	Height: 79.45mm(3.13"); Diameter: 42mm(1.65")
Connector	Direct Mount N type (M)
Housing Material	UV Resistant ABS
Base Material	Nickel Plated Zinc Alloy
Weight (g)	130
Rec. Torque for Mounting	4.018 N·m
Max. Torque for Mounting	9.8 N·m
Waterproof Rating	IP67
Operation Temperature	-40°C to 85°C
Humidity	Non-condensing 65°C 95% RH
Housing Rating	IK10




		5G/4G Bands		
Band Number	5GNR / FR1 / LTE / LTE-Advanced / WCDMA / HSPA / HSPA+ / TD-SCDMA / Cat M / NB			
	Uplink	Downlink	Covered	
1	UL: 1920 to 1980	DL: 2110 to 2170	✓	
2	UL: 1850 to 1910	DL: 1930 to 1990	✓	
3	UL: 1710 to 1785	DL: 1805 to 1880	✓	
4	UL: 1710 to 1755	DL: 2110 to 2155	✓	
5	UL: 824 to 849	DL: 869 to 894	✓	
7	UL: 2500 to 2570	DL:2620 to 2690	✓	
8	UL: 880 to 915	DL: 925 to 960	✓	
9	UL: 1749.9 to 1784.9	DL: 1844.9 to 1879.9	✓	
11	UL: 1427.9 to 1447.9	DL: 1475.9 to 1495.9	✓	
12	UL: 699 to 716	DL: 729 to 746	✓	
13	UL: 777 to 787	DL: 746 to 756	✓	
14	UL: 788 to 798	DL: 758 to 768	✓	
17	UL: 704 to 716	DL: 734 to 746	✓	
18	UL: 815 to 830	DL: 860 to 875	✓	
19	UL: 830 to 845	DL: 875 to 890	✓	
20	UL: 832 to 862	DL: 791 to 821	✓	
21	UL: 1447.9 to 1462.9	DL: 1495.9 to 1510.9	✓	
22	UL: 3410 to 3490	DL: 3510 to 3590	✓	
23	UL:2000 to 2020	DL: 2180 to 2200	✓	
24	UL:1625.5 to 1660.5	DL: 1525 to 1559	✓	
25	UL: 1850 to 1915	DL: 1930 to 1995	✓	
26	UL: 814 to 849	DL: 859 to 894	✓	
27	UL: 807 to 824	DL: 852 to 869	✓	
28	UL: 703 to 748	DL: 758 to 803	✓	
29	UL: -	DL: 717 to 728	✓	
30	UL: 2305 to 2315	DL: 2350 to 2360	✓	
31	UL: 452.5 to 457.5	DL: 462.5 to 467.5	×	
32	UL: -	DL: 1452 – 1496	✓	
35		✓		
38		✓		
39		✓		
40		✓		
41		✓		
42		✓		
43	3400 to 3600 3600 to 3800		✓	
48	3550 to 3700		✓	
66	UL: 1710-1780	DL: 2110-2200	✓	
71		617 to 698	✓	
74/75/76		1427 to 1518	✓	
77		3300 to 4200	✓	
78	3300 to 4200 ✓			
79		✓		




3. Antenna Characteristics

3.1 Return Loss




3.2 Efficiency






3.3 Average Gain




3.4 Peak Gain





4. Radiation Patterns

4.1 Test Setup





On 30*30cm Ground Plane



4.2 3D and 2D Radiation Patterns


652MHz









751MHz









890MHz









1470MHz









1805MHz









1990MHz









2595MHz









3550MHz









5530MHz








5. Mechanical Drawing (Units: mm)





6. Installation




Recommended torque for mounting is 4.018 N.m or 41 kgf.cm Maximum torque for mounting is 9.8 N.m or 100 kgf.cm




7. Packaging


1 No. TLS.01.1F11 per small box Box Dimensions - 66 x 66 x 115mm Weight - 170g



1 Outer Carton Carton Dimensions - 430 x 380 x 280mm 60 pcs TLS.01.1F11 per carton Weight - 10.59Kg



Pallet Dimensions 1100*1100*1550mm 30 Cartons per Pallet 10 Cartons per layer 3 Layers





Changelog for the datasheet

SPE-17-8-042 - OMB.868.B12F21

Revision: D (Current Version)		
Date:	2022-09-01	
Changes:	Updated specifications	
Changes Made by:	Cesar Sousa	

Previous Revisions

Revision: C		
Date:	2019-11-18	
Changes:	Included 5G data	
Changes Made by:	Jack Conroy	

Revision: B		
Date:	2017-03-30	
Changes:	Included LTE Table	
Changes Made by:	Andy Mahoney	

Revision: A (Original First Release)		
Date:	2015-10-11	
Notes:	Initial Release	
Author:	Jack Conroy	



www.taoglas.com

