



#### Hercules

Part No: IS.01.B.305111

#### **Description**

433 MHz Heavy Duty Screw Mount Antenna

#### **Features:**

Hercules Screw-Mount
OdBi ISM 433 MHz Band
Cable: 3m CFD200
Connector: SMA (M)
29mm\*49mm (Diameter
IP65 Rated Enclosure
RoHS & REACH Complian



3. Antenna Characteristics 4  4. Radiation Patterns 8  5. Mechanical Drawing 23  6. Installation 24		3
5. Mechanical Drawing 23 5. Installation 24 7. Packaging 25	<ol> <li>Specification</li> <li>Antenna Characteristics</li> </ol>	
7. Packaging 25	4. Radiation Patterns	8
7. Packaging 25	5. Mechanical Drawing	23
	6. Installation	24
Changelog 26	7. Packaging	25
	Changelog	26

Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein. Reproduction, use or disclosure to third parties without express permission is strictly prohibited.











### 1. Introduction



The IS.01 is a high performance 433MHz thread mount antenna for external use on mesh Networks, vehicles and outdoor and indoor assets. It is designed for heavy duty work with extra thick threads. Durable UV resistant PC housing is IP65 rated, resistant to vandalism and direct attack. At only 29mm high it complies with the latest EU directives for vehicle height restrictions, whilst also enabling covert operation with a diameter of 49mm.



# 2. Specification

	Electrical								
Band	Frequency (MHz)	Measurement	Efficiency (%)	Average Gain (dB)	Peak Gain (dBi)	Impedance	Polarization	Radiation Pattern	Input power
411.5MHz	411-412	30cmX30cm Ground Plane	67.1	-1.73	4.52			ear Omni	5W
411311111	111 112	Freespace	41.0	-3.87	0.82				
420MHz	<b>420MHz</b> 419-421	30cmX30cm Ground Plane	62.3	-2.05	4.53	50 Ω Linea	Linear		
72011112		Freespace	48.3	-3.16	2.36	30 11	Elifedi	O.I.III	3
<b>433MHz</b> 432	432-434	30cmX30cm Ground Plane	56.0	-2.52	4.47				
	.52 151	Freespace	65.2	-1.85	3.45				


Mechanical Mechanical		
Dimensions	Height=29mm x Diameter=49mm	
Material	UV Resistant PC	
Connector	SMA Male (Fully Customizable)	
Cable	3m CFD-200 (Fully Customizable)	
Base and Thread	Nickel plated steel	
Weather-proof gasket	CR4305 foam with 3M9448B double-side adhesive	
Thread Diameter	18mm	
Sealant	Rubber Stopper	


<b>Environmental</b>		
Waterproof Rating	IP65	
Operation Temperature	-40°C to +85°C	
Relative Humidity	Non-condensing 65 C 95% RH	
Corrosion	5% NACI for 48hrs- Nickel plated steel base and thread	
Shock (Drop Test)	1m drop on concrete 6 axes	
Cable Pull 8 kgf		




## 3. Antenna Characteristics

### 3.1 Test Setup











30x30cm Ground Plane



#### 3.2 Return Loss




#### 3.3 VSWR







### 3.4 Efficiency



#### 3.5 Average Gain












# 4. Radiation Patterns

### 4.1 Test Setup











30x30cm Ground Plane




#### 4.2 30cmX30cm Ground Plane Patterns at 410 MHz









### 4.3 Freespace Patterns at 410 MHz









#### 4.4 30cmX30cm Ground Plane Patterns at 411 MHz









### 4.5 Freespace Patterns at 411 MHz









#### 4.6 30cmX30cm Ground Plane Patterns at 414 MHz









### 4.7 Freespace Patterns at 414 MHz









#### 30cmX30cm Ground Plane Patterns at 415 MHz









### 4.9 Freespace Patterns at 415 MHz









#### 4.10 30cmX30cm Ground Plane Patterns at 420 MHz









### 4.11 Freespace Patterns at 420 MHz









#### 4.12 30cmX30cm Ground Plane Patterns at 424 MHz









### 4.13 Freespace Patterns at 424 MHz









#### 4.14 30cmX30cm Ground Plane Patterns at 433 MHz









### 4.15 Freespace Patterns at 433 MHz









# Mechanical Drawing






Side View



	◬			
		Name	Finish	QTY
	1	Housing	Black	1
	2	Closed Cell Foam	Black	1
	3	3M Double Adhesive	White Liner	1
	4	Metal Base	Ni Plated	1
	5	Rubber Stopper	Black	1
	6	Outer Nut Cover	Black	1
	7	M18 Inner Nut Cut	Zn Plated	1
⇘	8	CFD200 Coaxial Cable	Black	1
	9	Heat Shrink Tube(433 MHz)	Yellow Tube/Block Test	1
	10	SMA(M)ST	Au Plated	1




# 6. Installation






# 7. Packaging


1 pcs IS.01.B.305111 per PE Bag Bag Dimensions - 280 x 180 mm Weight - 214g




10 pcs IS.01.B.305111 per PE Large Bag Bag Dimensions - 520x 360mm Weight - 2.2kg



50 pcs IS.01.B.305111 per carton Carton - 430 x 380 x 280mm Weight - 11.3Kg



Pallet Dimensions 120x 100 x 132cm 24 Cartons per Pallet 6 Cartons per layer 4 Layers





#### Changelog for the datasheet

#### SPE-13-8-004- IS.01.B.305111

Revision: I (Current Version)		
Date:	2023-08-04	
Changes:	Updated data	
Changes Made by:	Gary West	

#### **Previous Revisions**

Revision: H	
Date:	2023-07-25
Changes:	Updated Antenna Specifications Updated Radiation Patterns
Changes Made by:	Aswin Biju

Revision: C	
Date:	2014-09-25
Changes:	changed to NFC200
Changes Made by:	AINE DOYLE

Revision: G (Current Version)		
Date:	2021-11-18	
Changes:	Format Change, MSL	
Changes Made by:	Erik Landi	

Revision: B	
Date:	2013-02-06
Changes:	
Changes Made by:	STAFF

Revision: F	
Date:	2021-02-09
Changes:	
Changes Made by:	Jack Conroy

Revision: A (Original First Release)		
Date:	2012-01-21	
Notes:	Initial Release	
Author:	STAFF	

Revision: E	
Date:	NA
Changes:	
Changes Made by:	STAFF

Revision: D	
Date:	2016-12-23
Changes:	Updated with revised salt spray info and disclaimer
Changes Made by:	Andy Mahoney





www.taoglas.com

