

www.taoglas.com

25 x 25 x 4.5mm Wi-Fi/Bluetooth Patch

0

Part No: WLP.2450.25.4.A.02

Description

25*25*4.5mm Wi-Fi/Bluetooth 2450MHz Patch

Features:

2.4GHz Wi-Fi/Bluetooth 5dBi Peak gain Pin Type with adhesive for ease of mounting Automotive IATF16949 Production and Quality Approved Dimensions: 25*25*4.5mm RoHS & Reach Compliant

SPE-11-8-033-N



1.	Introduction	2
2.	Specification	3
3.	Antenna Characteristics	4
4.	Radiation Patterns	7
5.	Mechanical Drawing	9
6.	Evaluation Board Mechanical Drawing	10
7.	Packaging	11
8.	Antenna Integration Guide	12

Changelog

15

Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein. Reproduction, use or disclosure to third parties without express permission is strictly prohibited.





Introduction



This WLP.25 patch antenna for ISM, Wi-Fi, Bluetooth and Zigbee is based on smart XtremeGain[™] technology. It is mounted via pin and double-sided adhesive and has been selected as optimal solution for the 50 x 50mm ground plane. This passive patch offers typical gain response from 5 dBi and a higher gain can be achieved, depending on the Ground Plane, the space available and clearance afforded. The WLP.25's high gain makes it a perfect solution for metering and remote monitoring applications; it can deliver longer range than smaller chip antennas.

Many module manufacturers specify peak gain limits for any antennas that are to be connected to that module. Those peak gain limits are based on free-space conditions. In practice, the peak gain of an antenna tested in free-space can degrade by at least 1 or 2dBi when put inside a device. So ideally you should go for a slightly higher peak gain antenna than mentioned in the module specification to compensate for this effect, giving you better performance.

Upon testing any of our antennas with your device and a selection of appropriate layout, integration technique, or cable, Taoglas can make sure any of our antennas' peak gain will be below the peak gain limits. Taoglas can then issue a specification and/or report for the selected antenna in your device that will clearly show it complying with the peak gain limits, so you can be assured you are meeting regulatory requirements for that module.

For example, a module manufacturer may state that the antenna must have less than 2dBi peak gain, but you don't need to select an embedded antenna that has a peak gain of less than 2dBi in free-space. This will give you a less optimized solution. It is better to go for a slightly higher free-space peak gain of 3dBi or more if available. Once that antenna gets integrated into your device, performance will degrade below this 2dBi peak gain due to the effects of GND plane, surrounding components, and device housing. If you want to be sure, contact Taoglas and we will test. Choosing a Taoglas antenna with a higher peak gain than what is specified by the module manufacturer and enlisting our help will ensure you are getting the best performance possible without exceeding the peak gain limits.

This antenna can be tuned for a custom device environment, subject to NRE and MOQ. For further information please contact your regional Taoglas customer support team.



2. Specification

Wi-Fi Electrical								
Band	Frequency (MHz)	Efficiency (%)	Average Gain (dB)	Peak Gain (dBi)	Impedance	Polarization	Radiation Pattern	Max. input power
Wi-Fi – 2.4GHz	2400-2500	90.5	-0.39	5.77	50 Ω	Linear	Omni	2W

Mechanical		
Dimensions	25 x 25 x 4.5 mm	
Pin Length	2.4 mm	
Material	Ceramic	
Ground Plane size	50 x 50 mm	

Environmental		
Temperature Range	-40°C to +105°C	
Humidity	Non-condensing 65°C 95% RH	

*Tested on a 50x50mm Ground Plane







3.





SPE-11-8-033-M











4.







4.2 WLP.2450.25.4.A.02 Patterns at 2450 MHz for Gtotal







Mechanical Drawing

5.





Evaluation Board Mechanical Drawing



6.



7. Packaging



SPE-11-8-033-M



8. Antenna Integration Guide





8.1 Schematic and Symbol Definition

The circuit symbol for the antenna is shown below. The antenna has 1 pin as indicated below.



8.2 Antenna Integration

The antenna should be placed at the center of the ground plane with a length and width of 50mm. Maintaining a square symmetric ground plane shape and symmetric environment around the antenna is critical to maintaining this antenna's high performance.



Top Side w/ Solder Mask

Top Side w/o Solder Mask



8.3 PCB Layout

The footprint and clearance on the PCB must comply with the antenna specification. The PCB layout shown in the diagram below demonstrates the antenna footprint.



Topside

Bottom Side





Topside



Bottom Side



Changelog for the datasheet

SPE-11-8-033 - WLP.2450.25.4.A.02

Revision: M (Current Version)		
Date:	2023-05-18	
Changes:	Full datasheet Update	
Changes Made by:	Gary West	

Previous Revisions

Revision: L (Current Version)		
Date:	2021-08-23	
Changes:	MSL removed form spec table	
Changes Made by:	Gary West	

Revision: G		
Date:	2016-08-16	
Changes:	Amended Pin Length	
Changes Made by:	Andy Mahoney	

Revision: K		
Date:	2021-07-13	
Changes:	Added Moisture Sensitivity Level	
Changes Made by:	Gary West	

Revision: F	
Date:	2015-12-08
Changes:	Amended Polarization
Changes Made by:	Aine Doyle

Revision: J		
Date:	2021-07-01	
Changes:	Updated data table	
Changes Made by:	Jack Conroy	

Revision: E		
Date:	2015-03-04	
Changes:	Added Note on Gain	
Changes Made by:	Aine Doyle	

Revision: I			
Date:	2020-03-27		
Changes:	Updated Template and polarization		
Changes Made by:	Jack Conroy		

Revision: D	
Date:	2013-04-24
Changes:	Packaging Details Updated
Changes Made by:	Technical Writer

Revision: H	
Date:	2017-03-23
Changes:	Drawing updated
Changes Made by:	Andy Mahoney

Revision: C	
Date:	2012-02-04
Changes:	Packaging Details Updated
Changes Made by:	Technical Writer



Previous Revisions

Revision: B	
Date:	2011-07-11
Changes:	Updated Data
Changes Made by:	Technical Writer

Revision: A (Original First Release)	
Date:	2007-03-01
Notes:	
Author:	Technical Writer





www.taoglas.com