

8 nV/√Hz Noise, RRO, Precision Instrumentation Amplifier

Features

- Gain set with one external resistor (Gain range 1 to 10,000)
- High CMRR: 105 dB min (G = 1, Grade B)
95 dB min (G = 1, -40 °C to +125 °C, Grade B)
- Low Input Offset Voltage: 25 μV max (Grade B)
- Low Input Offset Drift: 0.3 μV/°C
- Low Input Bias Current: 5 pA
- Low Noise: 8 nV/√Hz
- 2 μV_{P-P} input noise (0.1 Hz to 10 Hz, G = 1)
- Bandwidth: 625 kHz (G = 10)
- Supply Current: 3.3 mA
- Supply Voltage: ±2.4 V to ±18 V
- Specified Temperature Range: -40 °C to +125 °C


Applications

- Precision data acquisition
- Instrumentation
- Sensor signal conditioning
- Industrial control
- Communication systems
- Smart grid

ZJA3600 Product Family

Part Number	Gain Setting	
	G = 1 + 49.4 kΩ/R _G	G = 1 + 50 kΩ/R _G
Classic pinout	ZJA3600	ZJA3618
	ZJA3610 (G ≥ 10)	ZJA3608 (G ≥ 10)
Optimized pinout	ZJA3601	ZJA3619
	ZJA3611 (G ≥ 10)	ZJA3609 (G ≥ 10)

Application Examples



General Description

The ZJA3600/ZJA3618 is a precision, low-noise instrumentation amplifier that can be used to set the gain range from 1 to 10,000 with a single external resistor.

The ZJA3600/ZJA3618 is based on classic three-op-amp structure to provide high common-mode rejection ratio (CMRR) over 120 dB at a gain of 10. This allows it to accurately amplify useful signals in the presence of large external interference, which is a common situation in precision data acquisition, bridge sensor interface, thermocouples, and medical signal acquisition (such as ECG, EEG, etc.). The ZJA3600/ZJA3618 also guarantees a CMRR of over 95 dB (G = 1, Grade B) over a temperature range of -40 °C to +125 °C, providing a solid foundation for applications requiring guaranteed performance over a wide temperature range. This is an outstanding feature of the ZJA3600/ZJA3618.

The ZJA3600/ZJA3618 has both excellent DC and AC performances. Its input offset voltage is better than 25 μV (Grade B), its drift is typically 0.3 μV/°C, and its input bias current is around 5 pA. This simplifies system calibration costs. The noise is 8 nV/√Hz at 1 kHz, and the 0.1 Hz to 10 Hz noise is 2 μV_{P-P} (G = 1), making it very suitable for the first stage of precision circuits. The ZJA3600/ZJA3618 is a rail-to-rail output instrumentation amplifier, which can maximize the use of the ADC input range. The bandwidth is 625 kHz at a gain of 10, the slew rate is 2 V/μs, and the 0.01% settling time is 6.5 μs. This makes it suitable for precision multi-channel switching data acquisition systems.

The ZJA3600/ZJA3618 uses classic pinout (the gain-setting resistor is connected to pins 1 and 8). The ZJA3600/ZJA3618 performance is specified over a wide temperature range of -40 °C to +125 °C. Its supply voltage is from ±2.4 V to ±18 V. The ZJA3600/ZJA3618 is available in 8-lead SOIC package.

Typical Performance Characteristics




Table of contents

Features	1	Input Protection	17
Applications	1	Reference Terminal	17
ZJA3600 Product Family	1	Power Supply Regulation and Bypassing.....	17
General Description.....	1	Grounding.....	18
Application Examples	1	Over Temperature Protection	18
Typical Performance Characteristics	1	ZJA3600/ZJA3618 Comparison to Zero-drift	
Table of contents	2	Instrumentation Amplifiers	19
Version (Release B)	3	Applications and Implementation	20
Revision History	3	Bridge Circuit Interface.....	20
Pin Configurations and Function Descriptions.....	4	Building Precision Current Source with	
Absolute Maximum Ratings	5	ZJA3600/ZJA3618.....	20
Thermal Resistance	5	Precision Current Sensing.....	21
Specifications	6	Layout Guidelines	23
Typical Performance Characteristics	9	Layout Example.....	24
Theory of Operation.....	14	Outline Dimensions	26
Gain Selection.....	15	Ordering Guide.....	27
Offset Voltage	16	Orderable Device Explanation	27
Input Bias Current Return Path.....	16	Related Parts	28

Version (Release B)¹

Revision History

May 2024 - Release B

Added ZJA3618

Changes to "Specifications"

September 2023 – Release A

¹ Information furnished by ZJW Microelectronics is believed to be accurate and reliable. However, no responsibility is assumed by ZJW Microelectronics for its use, nor for any infringements of patents or other rights of third parties that may result from its use. Specifications subject to change without notice. No license is granted by implication or otherwise under any patent or patent rights of ZJW Microelectronics. Trademarks and registered trademarks are the property of their respective owners.

Pin Configurations and Function Descriptions




Figure 1. ZJA3600/ZJA3618 Pin Configuration (8-lead SOIC)

Mnemonic	Pin No.	I/O ¹	Description
R _G	1	AI	Gain setting pin. Place a gain resistor between pin 1 and pin 8
-IN	2	AI	Inverting input
+IN	3	AI	Non-inverting input
-V _s	4	P	Negative power supply
REF	5	AI	Reference input. This pin must be driven by a low impedance source
OUT	6	AO	Output
+V _s	7	P	Positive power supply
R _G	8	AI	Gain setting pin. Place a gain resistor between pin 1 and pin 8

¹ AI: Analog Input; P: Power; AO: Analog Output.

Absolute Maximum Ratings¹

Parameter	Rating
Supply Voltage	±20 V
Input Voltage	±Vs
Input Current ²	±10 mA
Differential Input Voltage (G = 1 to10)	(+Vs) - (-Vs)
Output Short-Circuit Duration to GND ³	Continuous
Operating Temperature Range	-40 °C to 125 °C
Storage Temperature Range	-65 °C to 150 °C
Maximum Reflow Temperature ⁴	150 °C
Lead Temperature, Soldering (10 sec)	260 °C
Electrostatic Discharge (ESD) ⁵	
Human Body Model (HBM) ⁶	3 kV
Charged Device Model (CDM) ⁷	2 kV

Thermal Resistance⁸

Package Type	θ _{JA}	θ _{JC}	Unit
SOIC-8	158	43	°C/W

¹ These ratings apply at 25 °C, unless otherwise noted. Note that stresses above those listed under Absolute Maximum Ratings may cause permanent damage to the device. This is a stress rating only; functional operation of the device at these or any other conditions above those indicated in the operational section of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

² There are clamping diodes between the input pins and the power pins, and also between each other. When the input signal exceeds the supply rail by 0.3 V, the input current is limited to 10 mA.

³ Limited by Over Temperature Protection (OTP).

⁴ IPC/JEDEC J-STD-020 Compliant

⁵ Charged devices and circuit boards can discharge without detection. Although this product features patented or proprietary protection circuitry, damage may occur on devices subjected to high energy ESD. Therefore, proper ESD precautions should be taken to avoid performance degradation or loss of functionality.

⁶ ANSI/ESDA/JEDEC JS-001 Compliant

⁷ ANSI/ESDA/JEDEC JS-002 Compliant

⁸ θ_{JA} addresses the conditions for soldering devices onto circuit boards to achieve surface mount packaging.

Specifications

The ● denotes the specification which apply over the specified temperature range, otherwise specifications are at $V_S = \pm 15\text{ V}$, $V_{REF} = 0\text{ V}$, $G = 1$, $R_L = 2\text{ k}\Omega$, $T_A = 25\text{ }^\circ\text{C}$.

Parameter	Symbol	Conditions	Min	Typ	Max	Unit
GAIN		ZJA3600: $G = 1 + (49.4\text{ k}\Omega/R_G)$ ZJA3618: $G = 1 + (50\text{ k}\Omega/R_G)$				
Range Of Gain			1		10,000	V/V
Gain Error	GE	$V_{OUT} = \pm 10\text{ V}$				
G = 1		B Grade	●	0.0001	0.001 0.003	% %
		A Grade			0.01	%
G = 10		B Grade	●	0.01	0.10 0.25	% %
		A Grade			0.15	%
G = 100		B Grade	●	0.01	0.10 0.25	% %
		A Grade			0.15	%
G = 1,000		B Grade	●	0.01	0.10 0.25	% %
		A Grade			0.15	%
Gain Nonlinearity		$V_{OUT} = -10\text{ V to }+10\text{ V}$				
G = 1 to 10		$R_L = 10\text{ k}\Omega$		0.5	5	ppm
G = 100		$R_L = 10\text{ k}\Omega$			10	ppm
G = 1000		$R_L = 10\text{ k}\Omega$			20	ppm
G = 1 to 100		$R_L = 2\text{ k}\Omega$			20	ppm
Gain vs temperature						
G = 1		B Grade	●	0.1	0.5	ppm/ $^\circ\text{C}$
		A Grade	●	0.3	1	ppm/ $^\circ\text{C}$
G > 1 ¹			●	-50	10 50	ppm/ $^\circ\text{C}$
OFFSET VOLTAGE						
Input Offset Voltage	V_{OSI}	B Grade	●	5	25 85	μV μV
		A Grade	●		50 110	μV μV
Average TC	TCV_{OSI}		●		0.6	$\mu\text{V}/^\circ\text{C}$

¹ The values specified for $G > 1$ do not include the effects of the external gain-setting resistor, R_G .







Parameter	Symbol	Conditions	Min	Typ	Max	Unit
Output Offset Voltage	V_{OSO}	B Grade	•	30	150	μV
		A Grade	•		200	μV
Average TC	TCV_{OSO}	B Grade	•		300	$\mu\text{V}/^\circ\text{C}$
		A Grade	•		500	$\mu\text{V}/^\circ\text{C}$
POWER SUPPLY REJECTION RATIO		$PSRR$	$V_S = \pm 2.4 \text{ V to } \pm 18 \text{ V}$			
G = 1		B Grade		110	130	dB
		A Grade		100	120	dB
G = 10		B Grade		130	140	dB
		A Grade		120	130	dB
G = 100		B Grade		130	140	dB
		A Grade		120	130	dB
G = 1,000		B Grade		140	150	dB
		A Grade		130	140	dB
INPUT BIAS CURRENT						
Input Bias Current	I_B			5	25	pA
Average TC	TCI_B	•		1		$\text{pA}/^\circ\text{C}$
Input Offset Current	I_{OS}			2	20	pA
Average TC	TCI_{OS}	•		1		$\text{pA}/^\circ\text{C}$
INPUT CHARACTERISTICS						
Input Impedance	R_{IN}/C_{IN}	Differential Mode		100/2		$\text{G}\Omega/\text{pF}$
		Common Mode		100/2		$\text{G}\Omega/\text{pF}$
Input Operating Voltage Range ¹	IVR	$V_S = \pm 2.4 \text{ V to } \pm 15 \text{ V}$		$-V_S+0.2$	$+V_S-1.1$	V
Common-ode Rejection Ratio	CMRR	DC to 60 Hz, $V_{CM} = -10 \text{ V to } +10 \text{ V}$				
G = 1		B Grade	•	105	120	dB
		A Grade		94		dB
		A Grade		95		dB
G = 10		B Grade		120	140	dB
		A Grade		115		dB
G = 100		B Grade		140	150	dB
		A Grade		135		dB
G=1,000		B Grade		140	150	dB
		A Grade		140		dB

¹ One input is connected to ground.

Parameter	Symbol	Conditions	Min	Typ	Max	Unit
OUTPUT CHARACTERISTICS						
Output Swing		$V_s = \pm 2.4 \text{ V to } \pm 15 \text{ V}, R_L = 2 \text{ k}\Omega$	$-V_s+0.3$		$+V_s-0.3$	V
Short-Circuit Current	I_{SC}	source		90		mA
		sink		50		mA
DYNAMIC PERFORMANCE						
Small Signal Bandwidth, -3 dB		$G = 1$		3200		kHz
		$G = 10$		625		kHz
		$G = 100$		70		kHz
		$G = 1000$		9		kHz
Slew Rate	SR		0.75	2		V/ μ s
Settling Time (to 0.01 %)	t_s	$G = 1$ to 10, 0 to 10 V step		6.5		μ s
		$G = 100$, 0 to 10 V step		23		μ s
		$G = 1,000$, 0 to 10 V step		213		μ s
NOISE PERFORMANCE						
Voltage Noise		Referred-To-Input (RTI) = $\sqrt{e_{ni}^2 + (e_{no}/G)^2}$				
		$f = 1 \text{ kHz}$				
Input Voltage Noise	e_{ni}			8		nV/ $\sqrt{\text{Hz}}$
Output Voltage Noise	e_{no}			75		nV/ $\sqrt{\text{Hz}}$
RTI		$f = 0.1 \text{ Hz to } 10 \text{ Hz}$				
		$G = 1$		2		μ V _{P-P}
		$G = 10$		0.9		μ V _{P-P}
		$G = 100$ to 1000		0.9		μ V _{P-P}
Input Current Noise		$f = 1 \text{ kHz}$		0.8		fA/ $\sqrt{\text{Hz}}$
		0.1 Hz to 10 Hz		6		pA _{P-P}
REFERENCE INPUT						
R_{IN}		$V_{IN+}, V_{IN-}, V_{REF} = 0$		10		k Ω
I_{IN}				0.003	0.03	μ A
Voltage Range			$-V_s+0.2$		$+V_s-1.1$	V
Reference Gain to Output				1 ± 0.0001		V/V
POWER SUPPLY						
Operating Range			± 2.4		± 18	V
Quiescent Current	I_{SY}			3.3	3.8	mA
					3.8	mA
TEMPERATURE RANGE						
		Specified Temperature Range	-40		125	$^{\circ}\text{C}$

Typical Performance Characteristics

Unless otherwise stated, $T_A = 25\text{ }^\circ\text{C}$, $V_S = \pm 15\text{ V}$, $R_L = 2\text{ k}\Omega$.






Figure 8. . Input Bias Current & Offset Current vs. Temperature




Figure 9. Input Common-Mode Voltage vs. Output Voltage (G = 1)




Figure 10. Input Common-Mode Voltage vs. Output Voltage (G = 100)




Figure 11. Positive Power Supply Rejection Ratio (PSRR) vs. Frequency, RTI (G = 1 to 1000)




Figure 12. Negative Power Supply Rejection Ratio (PSRR) vs. Frequency, RTI (G = 1 to 1000)




Figure 13. Gain vs. Frequency




Figure 14. Common Mode Rejection Ratio (CMRR) vs. Frequency (RTI)




Figure 15. Common Mode Rejection Ratio (CMRR) vs. Temperature




Figure 16. Input Voltage Limit vs. Supply Voltage (G = 1)




Figure 17. Output Voltage Swing vs. Load Resistance




Figure 18. Output Voltage Swing vs. Supply Voltage (G = 1, $R_L = 10\text{ k}\Omega$)










Figure 19. Output Voltage Swing vs. Supply Voltage (G = 1, $R_L = 2\text{ k}\Omega$)






Figure 26. Small Signal Pulse Response
($G = 10$, $R_L = 2 \text{ k}\Omega$, $C_L = 100 \text{ pF}$)




Figure 27. Small Signal Pulse Response
($G = 100$, $R_L = 2 \text{ k}\Omega$, $C_L = 100 \text{ pF}$)




Figure 28. Small Signal Pulse Response
($G = 1000$, $R_L = 2 \text{ k}\Omega$, $C_L = 100 \text{ pF}$)

Theory of Operation




Figure 29. Simplified Schematic of ZJA3600/ZJA3618

The ZJA3600/ZJA3618 is a monolithic instrumentation amplifier based on the classic 3-op amp topology. The input stage consists of amplifiers A1 and A2, two trimmed 24.7 kΩ or 25 kΩ resistors are integrated. They are used along with an external resistor R_G , to set the gain. The amplified differential and common-mode signals are applied to a difference amplifier that rejects the common-mode voltage but amplifies the differential voltage. The difference amplifier employs innovations that result in low output offset voltage as well as low output offset voltage drift. The proprietary ZHIJINGTRIM[®] is used to trim these resistors and amplifiers, achieving a highly accurate instrumentation amplifier with gain error less than 0.1% and CMRR exceeding 105 dB ($G = 1$, Grade B).

The ZJA3600/ZJA3618 offers extremely high input impedance, low I_B (below 25 pA at room temperature and symmetrical for +IN and -IN), low I_B drift, low I_{OS} (lower than 1 nA from -40 °C to 125 °C), low input bias current noise, and extremely low voltage noise of $8 \text{ nV}/\sqrt{\text{Hz}}$.

The gain equation of the ZJA3600 is

$$G = 1 + \frac{49.4 \text{ k}\Omega}{R_G}$$

The gain equation of the ZJA3618 is

$$G = 1 + \frac{50 \text{ k}\Omega}{R_G}$$

Gain Selection

Placing a resistor across the R_G terminals set the gain of ZJA3600, which can be calculated by referring to Table 1 or by using the gain equation.

$$R_G = \frac{49.4 \text{ k}\Omega}{G - 1}$$

1 % Standard Table Value of R_G (Ω)	Calculated Gain	0.1 % Standard Table Value of R_G (Ω)	Calculated Gain
49.9 k	1.990	49.3 k	2.002
12.4 k	4.984	12.4 k	4.984
5.49 k	9.998	5.49 k	9.998
2.61 k	19.93	2.61 k	19.93
1.00 k	50.40	1.01 k	49.91
499	100.0	499	100.0
249	199.4	249	199.4
100	495.0	98.8	501.0
49.9	991.0	49.3	1003

Table 1. Commonly-Used Gains and Resistor Values

The ZJA3600 defaults to $G = 1$ when no gain resistor is used. Gain accuracy is determined by the absolute tolerance of R_G . The TC of the external gain resistor increases the gain drift of the instrumentation amplifier. Gain error and gain drift are kept to a minimum when the gain resistor is not used. Integrated instrumentation amplifiers, owing to their precise pre-trimming, generally boast superior gain accuracy and temperature stability compared to discrete solutions.

Unlike the traditional high-gain amplifiers with built-in precision resistors having a negative TC, the ZJA3600's embedded resistors feature a positive TC (10 ppm/°C), aligning with most external resistors. This enables achieving unparalleled system temperature coefficients, crucial for precision applications requiring gain above 1 over a wide temperature range.

Placing a resistor across the R_G terminals set the gain of ZJA3618, which can be calculated by referring to Table 2 or by using the gain equation.

$$R_G = \frac{50 \text{ k}\Omega}{G - 1}$$

1 % Standard Table Value of R_G (Ω)	Calculated Gain	0.1 % Standard Table Value of R_G (Ω)	Calculated Gain
49.9 k	2.002	49.9 k	2.002
12.4 k	5.032	12.4 k	5.032
5.62 k	9.897	5.56 k	9.993
2.61 k	20.16	2.64 k	19.94
1.02 k	50.02	1.02 k	50.02
511	98.85	505	100.0
249	201.8	252	199.4
100	501.0	100	501.0
49.9	1003	49.9	1003

Table 2. Commonly-Used Gains and Resistor Values

The ZJA3618 defaults to $G = 1$ when no gain resistor is used. Gain accuracy is determined by the absolute tolerance of R_G . The TC of the external gain resistor increases the gain drift of the instrumentation amplifier. Gain error and gain drift are kept to a minimum when the gain resistor is not used. Integrated instrumentation amplifiers, owing to their precise pre-trimming, generally boast superior gain accuracy and temperature stability compared to discrete solutions.

Unlike the traditional high-gain amplifiers with built-in precision resistors having a negative TC, the ZJA3600's embedded resistors feature a positive TC (10 ppm/°C), aligning with most external resistors. This enables achieving unparalleled system temperature coefficients, crucial for precision applications requiring gain above 1 over a wide temperature range.

Offset Voltage

The offset voltage of the ZJA3600/ZJA3618 is attributed to two sources, input offset voltage V_{OSI} and output offset voltage V_{OSO} . The V_{OSO} is divided by G when referred to the input. In practice, the V_{OSI} dominates at high gains, and the V_{OSO} dominates at low gains. V_{OSI} includes the offset voltage generated by input amplifiers A1 and A2; V_{OSO} is the offset voltage of amplifier A3. The total V_{OS} for a given gain is calculated as

$$\text{Total Error RTI } (V_{OS,RTI}) = V_{OSI} + \frac{V_{OSO}}{G}$$

$$\text{Total Error RTO } (V_{OS,RTO}) = G * V_{OSI} + V_{OSO}$$

ZJA3600/ZJA3618's low offset voltages eliminate the need for system-level calibration, reducing costs and improving efficiency.

Input Bias Current Return Path

Instrumentation amplifiers typically interface with high-impedance signal sources. The ZJA3600/ZJA3618 boasts an exceptional input bias current of under 25 pA at room temperature, a performance previously only found in expensive JFET amplifiers. Furthermore, it delivers this unmatched current level alongside significantly improved accuracy. When the source, such as a thermocouple, cannot provide a return current path, one should be created, as shown in Figure 30 and Figure 31.




Figure 30. ZJA3600/ZJA3618 Interfaces with Thermocouple




Figure 31. ZJA3600/ZJA3618 Interfaces with Transformer

When using ZJA3600/ZJA3618 for AC coupling, it is important to provide a return path to the input AC coupling capacitors. Otherwise, the input offset voltage will accumulate due to parasitic leakage and input currents, potentially causing the output to lock to a fixed voltage near the power rail. Figure 32 shows the correct connection for AC coupling, which utilizes a high-pass filter with a cutoff frequency determined by RC . And due to the differential inputs, the matching of R and C is crucial.




Figure 32. ZJA3600/ZJA3618 in AC Coupling Connection

Input Protection

The ZJA3600/ZJA3618 features a 3 kV ESD rating in the Human Body Model (HBM). As shown in Figure 29, each input of the ZJA3600/ZJA3618 has a current-limit circuit, protecting both the device itself and the system.

For applications where the ZJA3600/ZJA3618 encounters extreme overload voltages, as in cardiac defibrillators, external series resistors, and low leakage diode clamps, such as BAV199Ls, FJH1100s, or SP720s should be used.

Reference Terminal

The reference terminal REF defines the zero-output voltage and is especially useful when the load does not share a precise ground with the rest of the system. It can interface with pseudo-differential input ADCs easily, for example, ZJC2002 (pseudo-differential unipolar) and ZJC2003 (pseudo-differential bipolar).

As shown in Figure 29, the REF pin is directly connected to one end of the internally trimmed 10 k Ω resistor, and the output of the instrumentation amplifier is referenced to the voltage on the REF pin. When ZJA3600/ZJA3618 interfaces with ADC ZJC2002, which requires the output of the front-end circuit to be referenced to half of its supply voltage ($V_{DD}/2$). In this case, an external $V_{DD}/2$ source can be connected to the REF pin of ZJA3600/ZJA3618, which is very convenient.

Parasitic resistance should be kept to a minimum for optimum CMRR. To achieve the best performance, the REF pin should maintain a low source impedance, as parasitic resistance can adversely affect CMRR and gain accuracy. If the REF pin is not connected to a clean and low-impedance system ground, a precision op amp buffer (such as ZJA3000) between the REF pin and the signal source is recommended to achieve the best performance.

Power Supply Regulation and Bypassing

A stable dc voltage should be used to power the instrumentation amplifier. Noise on the supply pins can adversely affect performance. Bypass capacitors should be used to decouple the amplifier.

A low ESR 0.1 μ F capacitor should be placed close to each supply pin. High-quality surface-mount ceramic capacitors (such as X5R or X7R) are recommended. As shown in Figure 33, a 10 μ F tantalum capacitor can be used, and in most cases, it can be shared by other precision integrated circuits. Refer to the Layout Example section for specific layout examples.




Figure 33. Supply Decoupling, REF, and Output Referred to Local Ground

Although the ZJA3600/ZJA3618 is a very reliable chip with certain protection functions, it is generally recommended to power on the ZJA3600/ZJA3618 before applying the input signals.

Grounding

Star grounding is recommended for the ZJA3600/ZJA3618 circuit, as shown in Figure 33. Maintain low impedance for the REF pin because the output voltage of the ZJA3600/ZJA3618 is developed with respect to the potential on the REF. Place the decoupling capacitors as close to the power pins as possible to minimize the loop area.

In a multilayer PCB, use a large area ground plane if possible. Place analog signals on the layer above the ground plane.

In mixed-signal environments, low level analog signals need to be isolated from the noisy digital environment. Modern precision SAR ADCs have separate analog and digital ground, and they are all connected to the analog ground. When used with this type of ADC, the ZJA3600/ZJA3618 uses the analog ground as the reference.

The ZJA3600/ZJA3618 has a low bias current. To reduce leakage current, it is recommended to remove the ground plane below the signal traces of the two inputs. Refer to the Layout Examples section for specific examples.

Over Temperature Protection

Due to its high operating voltage (up to 36 V) and short-circuit current (source 90 mA and sink 50 mA), the ZJA3600/ZJA3618 can dissipate up to 2 W of power during use. As thermal resistance for various package formats typically exceeds 100 °C/W, self-heating and the risk of permanent damage from high temperatures are concerns in real-world applications. To address this, the ZJA3600/ZJA3618 incorporates an automatic over-temperature protection (OTP) function. When the chip temperature reaches 150 °C, OTP triggers, putting the chip into shutdown mode. Both input and output terminals enter a high-impedance state, significantly reducing power consumption and facilitating temperature drop. Once the chip cools down to 130 °C, OTP disengages, and the chip resumes normal operation.

ZJA3600/ZJA3618 Comparison to Zero-drift Instrumentation Amplifiers

ZJA3600/ZJA3618 is a continuous-signal processing instrumentation amplifier, unlike chopping/auto-zero-based zero-drift amplifiers reliant on non-continuous switch-based technology. These amplifiers contain a sampling capacitor at the input, causing the input bias current to exhibit periodic glitches invisible in datasheets due to averaging. Eliminating these glitches requires an output filter, significantly limiting their usable bandwidth and often restricting them to DC and near-DC signals. Adding a filter also adds complexity to system design. Additionally, tolerance of their internal sampling capacitors leads to variations in glitch amplitude across different ICs. More critically, their linearity (THD & THD+N) is often not great. While they may boast better low-frequency noise, this comes at the cost of transferring noise to the switching frequency, resulting in a noisy spectrum with large spike components. Consequently, their overall noise performance is often inferior to high-performance continuous sampling amplifiers like the ZJA3600/ZJA3618.

Furthermore, the usable bandwidth of zero-drift amplifiers is typically only 1/10 or 1/100 of what their datasheets suggest, severely limiting their usability. Their settling time and overload recovery time are also often much longer, making them unsuitable for multi-channel switching or applications with dynamic performance requirements.

Applications and Implementation

Bridge Circuit Interface

Bridge circuits are widely used in various sensing systems. Figure 34 shows how the ZJA3600/ZJA3618 interfaces with a bridge circuit, enabling its integration into a data acquisition system (DAS). Bridge circuits have different designs depending on the parameters being measured (excitation voltage V_{exc} , resistance R_b , and sensitivity, etc.), resulting in different electrical characteristics. The excitation voltage and resistance have the greatest impact on the interface circuit. As a general-purpose differential-to-single-ended input device, the instrumentation amplifier is very suitable for the interface of bridge circuit sensors. The excitation voltage determines the input common-mode voltage of the instrumentation amplifier as $V_{exc}/2$. It is necessary to pay attention to the supply voltage of the instrumentation amplifier to ensure that $V_{exc}/2$ is within the allowable input range. The wide supply voltage of ZJA3600/ZJA3618 provides flexibility in use, and its excellent common-mode rejection ratio (CMRR) and guaranteed temperature characteristics (ZJA3600/ZJA3618's CMRR is guaranteed in the $-40\text{ }^{\circ}\text{C}$ to $125\text{ }^{\circ}\text{C}$ range) ensure the accuracy of the circuit over the entire temperature range, simplifying system design. The resistance R_b has a significant impact on the instrumentation amplifier, and it is generally required that the instrumentation amplifier has high input impedance and low voltage noise. If R_b is higher than $100\text{ k}\Omega$, users need to carefully check the bias current and current noise of the instrumentation amplifier. The ZJA3600/ZJA3618's bias current is within 25 pA and current noise is $0.8\text{ pA}/\sqrt{\text{Hz}}$ at room temperature, making it ideal to interface with high-output impedance bridge circuits and ensuring system SNR (signal-to-noise ratio) and resolution.




Figure 34. ZJA3600 Interfaces with Bridge Circuit

Building Precision Current Source with ZJA3600/ZJA3618

Figure 35 illustrates the construction of a precision current source using a single ZJA3600/ZJA3618 instrumentation amplifier, one ZJA3000-1 precision operational amplifier and two resistors. This design offers flexibility with a supply voltage range of $\pm 2.4\text{ V}$ to $\pm 18\text{ V}$. The ZJA3600/ZJA3618's characteristics simplify setting the circuit's current output. The actual current output is equal to the set value minus the input bias current of the ZJA3000, which is within 25 pA at room temperature, making it often negligible.




Figure 35. Building Precision Current Source with ZJA3600/ZJA3618

Precision Current Sensing

The ZJA3600/ZJA3618 is often used for precision current sensing due to its high accuracy, wide bandwidth, low input bias current, and ease of use. As shown in Figure 36, the shunt resistor R_s is typically low, possibly a few Ohms, or even in the $m\Omega$ range. The ZJA3600/ZJA3618's high input impedance and input bias current of 25 pA or less allow it to detect currents as low as 1 nA; its low-frequency noise of $0.9 \mu V_{P-P}$ allows it to detect μV -level signals. The ZJA3600/ZJA3618 has a wide input range, allowing it to accurately measure input signals with a large dynamic range from μV to several volts. In general, current changes rapidly, so the ZJA3600/ZJA3618's wide bandwidth is very suitable. This is particularly beneficial in applications like motor control or battery monitoring, where current can fluctuate rapidly. On the other hand, the voltage V_m can be a high voltage varying at a certain frequency. In this case, the ZJA3600/ZJA3618's high CMRR is critical for accuracy. The ZJA3600/ZJA3618's CMRR performance with frequency is very good, with a several-fold improvement over traditional pin-out instrumentation amplifiers. This meets the new current sensing requirements of many emerging industries. For example, with the adoption of renewable energies, the frequency of current and voltage has increased. To maintain the same detection accuracy, the CMRR of the instrumentation amplifier must also be increased with frequency. The characteristics of the ZJA3600/ZJA3618 meet this new requirement, enabling systems to meet requirements without modifying hardware, which greatly accelerates the product iteration speed.

For applications that require long-term operation and large environmental temperature changes, the ZJA3600/ZJA3618's long-term stability and temperature drift characteristics are very valuable, making the design simpler and more reliable.

In some applications, the signal dynamic range is too big, and the accuracy or linearity of the instrumentation amplifier must be sacrificed by changing R_G to meet the needs of measuring the entire dynamic range. In this case, using digital potentiometers (digi-POTs) is not a good solution, because their temperature characteristics are often not very good. Engineers may consider the series and parallel connection of precision resistors, utilizing relays with good temperature characteristics to switch between ranges. Attention should be paid to wiring in such configurations.




Figure 36. Using ZJA3600/ZJA3618 for Precision Current Sensing

In precision current sensing, if a zero-drift instrumentation amplifier is used, the offset voltage caused by bias current glitch and high-frequency noise will limit the minimum detectable current, thereby limiting the detection accuracy. The available bandwidth of a zero-drift instrumentation amplifier is typically 1/10 to 1/100 of its data sheet bandwidth, which limits the available bandwidth of the current to be measured. This can often make it difficult to keep up with fast-changing currents, resulting in missed information or limiting the bandwidth of closed-loop systems. The longer settling time and lower slew rate of zero-drift instrumentation amplifiers will reduce the system's response speed. The poor linearity of zero-drift instrumentation amplifiers can make the design of control systems difficult or even impossible.

The ZJA3600/ZJA3618 is a good choice for precision current sensing applications. It offers a combination of high accuracy, wide bandwidth, low input bias current, and ease of use that is not available in other instrumentation amplifiers.

Layout Guidelines

For best operational performance of the device, use good PCB layout practices, including:

- Noise can propagate into analog circuitry through the power pins of the circuit as a whole and op amp itself. Bypass capacitors are used to reduce the coupled noise by providing low-impedance power sources local to the analog circuitry.
 - Connect low-ESR, 0.1- μ F ceramic bypass capacitors between each supply pin and ground, placed as close to the device as possible. A single bypass capacitor from V+ to ground is applicable for single-supply applications.
- Separate grounding for analog and digital portions of circuitry is one of the simplest and most-effective methods of noise suppression. One or more layers on multilayer PCBs are usually devoted to ground planes. A ground plane helps distribute heat and reduces EMI noise pickup. Make sure to physically separate digital and analog grounds paying attention to the flow of the ground current.
- In order to reduce parasitic coupling, run the input traces as far away from the supply or output traces as possible. If these traces cannot be kept separate, crossing the sensitive trace perpendicular is much better as opposed to in parallel with the noisy trace.
- Place the external components as close to the device as possible. As illustrated in Figure 40, keeping R_F, R_G and C_F close to the inverting input minimizes parasitic capacitance.
- Keep the length of input traces as short as possible. Always remember that the input traces are the most sensitive part of the circuit.
- Consider a driven, low-impedance guard ring around the critical traces. A guard ring can significantly reduce leakage currents from nearby traces that are at different potentials.
- Cleaning the PCB following board assembly is recommended for best performance.
- Any precision integrated circuit may experience performance shifts due to moisture ingress into the plastic package. Following any aqueous PCB cleaning process, baking the PCB assembly is recommended to remove moisture introduced into the device packaging during the cleaning process. A low temperature, post cleaning bake at 85 °C for 30 minutes is sufficient for most circumstances.

Layout Example




Figure 37. ZJA3620/ZJA3600/ZJA3618 Evaluation Board Schematic

The ZJA3600, ZJA3618 and ZJA3620 share the same evaluation board. During evaluation, a Kelvin connection, as shown in Figure 37, is typically not necessary. R7, R9, and R11 can be connected as needed, while R8, R10, and R12 can be selected based on the desired gain. In most cases, one of these paths is sufficient. For example, R7 could be set to 0 Ohms, and R8 could be assigned the resistance value calculated for the desired gain.




Figure 38. Layout of ZJA3600/ZJA3618/ZJA3620 Evaluation Board (Top Layer)




Figure 39. Layout of ZJA3600/ZJA3618/ZJA3620 Evaluation Board (Bottom Layer)

Outline Dimensions




Figure 40. 8-Lead SOIC Package Dimensions shown in millimeters

Ordering Guide

Model	Package	Orderable Device	Temperature Range (°C)	External Package
ZJA3600	SOIC-8	ZJA3600BSABT	-40 to 125	Tube
	SOIC-8	ZJA3600BSABR	-40 to 125	13" reel
	SOIC-8	ZJA3600ASABT	-40 to 125	Tube
	SOIC-8	ZJA3600ASABR	-40 to 125	13" reel
ZJA3618	SOIC-8	ZJA3618BSABT	-40 to 125	Tube
	SOIC-8	ZJA3618BSABR	-40 to 125	13" reel
	SOIC-8	ZJA3618ASABT	-40 to 125	Tube
	SOIC-8	ZJA3618ASABR	-40 to 125	13" reel

Orderable Device Explanation

ZJXXXXX X X X X X Q1

- Q1: Automotive Grade
- External Package: T = tube; R = reel
- Temperature range: A = -40 °C to 125 °C Automotive Grade 1; B = -40 °C to 125 °C; E = -40 °C to 85 °C
- Number of Pins: T = 6; A = 8; B = 10; D = 14; E = 16; P = 20;
- Package type: S = SOIC; U = MSOP, TSSOP, SOT; T = DFN, QFN
- Grade: B grade is better than A grade
- Base: R = Voltage reference; A = Amplifier; C = Data Converter; G = Switches and Multiplexers; M = Others

Related Parts

Part Number	Description	Comments
ADC		
ZJC2020	20-bit 350 kSPS SAR ADC	Fully differential input, SINAD 101.4 dB, THD -118 dB
ZJC2000/2010	18-bit 400 kSPS/200 kSPS SAR ADC	Fully differential input, SINAD 99.3 dB, THD -113 dB
ZJC2001/2011	16-bit 500 kSPS/250 kSPS SAR ADC	Fully differential input, SINAD 95.3 dB, THD -113 dB
ZJC2002/2012	16-bit 500 kSPS/250 kSPS SAR ADC	Pseudo-differential unipolar input, SINAD 91.7 dB, THD -105 dB
ZJC2003/2013		Pseudo-differential bipolar input, SINAD 91.7 dB, THD -105 dB
ZJC2004/2014	18-bit 400 kSPS/200 kSPS SAR ADC	Pseudo-differential unipolar input, SINAD 94.2 dB, THD -105 dB
ZJC2005/2015		Pseudo-differential bipolar input, SINAD 94.2 dB, THD -105 dB
ZJC2007/2017	14-bit 600 kSPS/300 kSPS SAR ADC	Pseudo-differential unipolar input, SINAD 85 dB, THD -105 dB
ZJC2008/2018		Pseudo-differential bipolar input, SINAD 85 dB, THD -105 dB
ZJC2100/1-18	18-bit 400 kSPS/200 kSPS 4-ch differential SAR ADC, SINAD 99.3 dB, THD -113 dB	
ZJC2100/1-16	16-bit 500 kSPS/250 kSPS 4-ch differential SAR ADC, SINAD 95.3 dB, THD -113 dB	
ZJC2102/3-18	18-bit 400 kSPS/200 kSPS 8-ch pseudo-differential SAR ADC, SINAD 94.2 dB, THD -105 dB	
ZJC2102/3-16	16-bit 500 kSPS/250 kSPS 8-ch pseudo-differential SAR ADC, SINAD 91.7 dB, THD -105 dB	
ZJC2102/3-14	14-bit 600 kSPS/300 kSPS 8-ch pseudo-differential SAR ADC, SINAD 85 dB, THD -105 dB	
ZJC2104/5-18	18-bit 400 kSPS/200 kSPS 4-ch pseudo-differential SAR ADC, SINAD 94.2 dB, THD -105 dB	
ZJC2104/5-16	16-bit 500 kSPS/250 kSPS 4-ch pseudo-differential SAR ADC, SINAD 91.7 dB, THD -105 dB	
DAC		
ZJC2541-18/16/14	18/16/14-bit 1 MSPS single channel DAC with unipolar output	Power on reset to 0 V (ZJC2541) or $V_{REF}/2$ (ZJC2543), 1 nV-S glitch, SOIC-8, MSOP-10/8, DFN-10 packages
ZJC2543-18/16/14		
ZJC2542-18/16/14	18/16/14-bit 1 MSPS single channel DAC with bipolar output	Power on reset to 0 V (ZJC2542) or $V_{REF}/2$ (ZJC2544), 1 nV-S glitch, SOIC-14/TSSOP-16/QFN-16 packages
ZJC2544-18/16/14		
Amplifier		
ZJA3000-1/2/4	Single/Dual/Quad 36 V low bias current precision Op Amps	3 MHz GBW, 35 μ V max Vos, 0.5 μ V/ $^{\circ}$ C max Vos drift, 25 pA max I _{bias} , 1 mA/Amplifier, input to V ₋ , RRO, 4.5 V to 36 V
ZJA3001-1/2/4	Single/Dual/Quad 36 V low bias current precision Op Amps	3 MHz GBW, 35 μ V max Vos, 0.5 μ V/ $^{\circ}$ C max Vos drift, 25 pA max I _{bias} , 1 mA/Amplifier, RRO, 4.5 V to 36 V
ZJA3512-2/4	Dual/Quad 36 V 7 MHz precision JFET Op Amps	7 MHz GBW, 35 V/ μ S SR, 50 μ V max Vos, 1 μ V/ $^{\circ}$ C max Vos drift, 2 mA/Amplifier, RRO, 9 V to 36 V
ZJA3600/1	36 V ultra-high precision in-amp	CMRR 105 dB min (G = 1), 25 pA max I _{bias} , 25 μ V max Vos _i , gain error 1 ppm max (G = 1), 3.3 mA I _q , ± 2.4 V to ± 18 V, -40 $^{\circ}$ C to 125 $^{\circ}$ C specified
ZJA3622/8	36 V low-cost precision in-amp	CMRR 93 dB min (G = 10), 0.5 nA max I _{bias} , 125 μ V max Vos _i , 625 kHz BW (G = 10), 3.3 mA I _q , ± 2.4 V to ± 18 V
ZJA3611, ZJA3609	36 V ultra-high precision wider bandwidth precision in-amp (min gain of 10)	CMRR 120 dB min (G = 10), 25 pA max I _{bias} , 25 μ V max Vos _i , 1.2 MHz BW (G = 10), 3.3 mA I _q , ± 2.4 V to ± 18 V, -40 $^{\circ}$ C to 125 $^{\circ}$ C specified
ZJA3676/7	Low power, G = 1 Single/Dual 36 V difference amplifier	Input protection to ± 65 V, CMRR 104 dB min, Vos 100 μ V max, gain error 15 ppm max, 500 kHz BW, 330 μ A/channel, 2.7 V to 36 V
ZJA3100	15 V precision fully differential amplifier	145 MHz GBW, 447 V/ μ S SR, 16-bit settling time 50 nS, 25 μ V max Vos, 4.6 mA I _q , 3 V to 15 V, SOIC/MS-8, QFN-16
Voltage Reference		
ZJR1004	40 V supply precision voltage reference	$V_{OUT} = 2.048/2.5/3/3.3/4.096/5/10$ V, 5 ppm/ $^{\circ}$ C max drift -40 $^{\circ}$ C to 125 $^{\circ}$ C
ZJR1000	15 V supply precision voltage reference	$V_{OUT} = 1.25/2.048/2.5/3/4.096/5$ V, 5 ppm/ $^{\circ}$ C max drift -40 $^{\circ}$ C to 125 $^{\circ}$ C
ZJR1001/2	5.5 V low power voltage reference (ZJR1001 with noise filter option)	$V_{OUT} = 2.5/3/4.096/5$ V, 5 ppm/ $^{\circ}$ C max drift -40 $^{\circ}$ C to 125 $^{\circ}$ C, $\pm 0.05\%$ initial error, 130 μ A, ZJR1001/2 in SOT23-6, ZJR1003 in SOIC/MS-8
ZJR1003		
Switches and Multiplexers		
ZJG4438/4439	36 V fault protection 8:1/dual 4:1 multiplexer	Protection to ± 50 V power on & off, latch-up immune, Ron 270 Ω , 14.8 pC charge injection, t _{ON} 166 nS, 10 V to 36 V