

CC6921

# High Performance, Hall Effect-Based Current Sensor IC with a Low-Resistance Conductor 5A/10A/20A/25A/30A/40A/50A/65A/75A/100A series

#### **GENERAL DESCRIPTION**

The CC6921 device is a high-performance current sensor based on Hall Effect. The device provides precise and economical solutions for AC or DC current sensing in industrial, commercial and communication equipment.

The CC6921 device consists of a precise, low-offset, linear Hall circuit with a copper conduction path located near the surface of the die. When current flows through the copper conduction path, a magnetic field generates. Meanwhile the Hall circuit converts this magnetic signal to output voltage signal. Internal copper conductor's resistance is typical  $0.45 m\Omega$ , which provides much less power loss than the universal resistor sampling method. Otherwise, its internal inherent insulation provides  $1000 V_{RMS}$  basic working isolation voltage and 3750 V (AC) insulation withstand voltage between the input current path and the secondary circuit.

The Hall circuit based on BiCOMS process integrates a high sensitivity Hall element, oscillator, Hall signal pre-amplifier, CrossChip® patented temperature compensation circuit, dynamic offset cancellation circuit, sensitivity trimming circuit and output amplifier.

Zero current output voltage is 50%VCC. When power supply voltage is 5V, the linear output voltage range is 0.2~4.8V, the linearity can reach 0.1%

CC6921 is available in SOP16W package. It's operating ambient temperature range is -40~125°C. Comply with ROHS requirements.


#### **FEATURES**

- ◆ Zero current output voltage is 50%VCC
- Current sensing range available:
   5A/10A/20A/25A/30A/40A/50A/65A/75A/100A
- 1.2MHz chopper frequency, high bandwidth, low noise, single ended analog output
- High isolation and withstand voltage (3750V(AC) isolation voltage between pins 1-8 and 9-16)
- lack Less power loss, internal conductor's resistance is 0.45mΩ
- High bandwidth, up to 250KHz, 1.2μs output rise time in response to step input current
- ◆ Total output error ±1% at T<sub>a</sub>=25°C and ±3% at T<sub>a</sub>=-40~125°C
- CrossChip® patented temperature compensation
- Outputs desensitized to mechanical stress
- Differential Hall structure, strong resistance to external magnetic interference
- ◆ ESD (HBM) 4000V
- ♦ Operating ambient temperature: -40~125°C

#### **APPLICATIONS**

- Motor controller
- ◆ Load detection and management
- Switch-mode power supplies
- Over-current fault protection












## **FUNCTION BLOCK DIAGRAM**




## **ORDERING INFORMATION**

Part No.	SENS. (mV/A)	Package	Packing Form
CC6921SO-5A	400	SOP16W	tape reel, 1000 pcs/reel
CC6921SO-10A	200	SOP16W	tape reel, 1000 pcs/reel
CC6921SO-20A	100	SOP16W	tape reel, 1000 pcs/reel
CC6921SO-25A	80	SOP16W	tape reel, 1000 pcs/reel
CC6921SO-30A	66.7	SOP16W	tape reel, 1000 pcs/reel
CC6921SO-40A	50	SOP16W	tape reel, 1000 pcs/reel
CC6921SO-50A	40	SOP16W	tape reel, 1000 pcs/reel
CC6921SO-65A	30.8	SOP16W	tape reel, 1000 pcs/reel
CC6921SO-75A	26.7	SOP16W	tape reel, 1000 pcs/reel
CC6921SO-100A	20	SOP16W	tape reel, 1000 pcs/reel
CC6921SO-YYA (Note1)	-	SOP16W	tape reel, 1000 pcs/reel

Note1: When YYA is within the range of 100A, customers can customize the range according to their needs.



## **PINOUT DIAGRAM**



Name	Number	Description	Name	Number	Description
IP+	1	Current Sampled +	NC	9	NC
IP+	2	Current Sampled +	VCC	10	Power Supply
IP+	3	Current Sampled +	NC	11	NC
IP+	4	Current Sampled +	VOUT	12	Analog Voltage Output
IP-	5	Current Sampled -	VZCR	13	Zero Current Reference
IP-	6	Current Sampled -	NC	14	NC
IP-	7	Current Sampled -	GND	15	Ground
IP-	8	Current Sampled -	NC	16	NC

## **ABSOLUTE MAXIMUM RATINGS**

Parameter	Symbol	Value	Unit
Power Supply	V <sub>CC</sub>	7	V
Output Voltage	V <sub>out</sub>	-0.3~VCC+0.3	V
Output Source Current	lout (source)	6	mA
Output Sink Current	lout (sink)	30	mA
Input current peak current (3 s)	<b>I</b> PEAK	100	Α
Input current continuous current	Icon	60	Α
Isolation Voltage	V <sub>ISO</sub>	3750	VAC
Operating Ambient Temperature	Ta	-40~125	°C
Junction Temperature	TJ	165	°C
Storage Temperature	Ts	-55~150	°C
Magnetic Flux Density	В	Not Limited	mT
Electrostatic Discharge Voltage (HBM)	ESD(HBM)	4000	V

**Note:** Stresses beyond those listed under *Absolute Maximum Ratings* may cause permanent damage to the device. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.



#### **ISOLATION CHARACTERISTICS**

Parameter	Symbol	Test Conditions	Value	Unit
Withstand isolation voltage	V <sub>ISO</sub>	Test method: 50 / 60Hz, 1min	3750	V <sub>RMS</sub>
Withstand isolation voltage	V <sub>TEST</sub>	V <sub>TEST</sub> t = 1s (100% production)		V <sub>RMS</sub>
Warking Voltage for Desig Inculation		Basic insulation	1414	V <sub>PK</sub> or VDC
Working Voltage for Basic Insulation	V <sub>WVBI</sub>	UL standard 62368-1:2014	1000	V <sub>RMS</sub>
Clearance	D <sub>cl</sub>	minimum distance through air from IP	7.8	mm
Clearance	D <sub>cl</sub>	leads to signal leads	7.0	111111
Maximum surge isolation voltage (Note 1)	imum surge isolation voltage (Note 1) V <sub>IOSM</sub> Tested 1.2us (rise) / 50us (width) One time		11k	$V_{PK}$
Surge Current (Note 2)	Isurge	Tested in compliance to IEC 61000-4-5 8µs (rise) / 20µs (width)	16	kA

Note1: Testing is carried out in air to determine the intrinsic surge immunity of the isolation barrier.

Note2: Certification pending.

#### RECOMMENDED OPERATING CONDITIONS

Parameter	Symbol	Min.	Max.	Unit
Input voltage (Note 1)	VIN+, VIN- (Note 1)	-1414	1414	V <sub>PK</sub>
Input current (DC / AC RMS) (Note 2)	IP	-50	50	Α
Power Supply	Vcc	4.5	5.5	V
Operation Temperature	T <sub>A</sub>	-40	125	°C

Note 1: Vin +, VIN – refers to the voltage of current input pins IP + and IP -, relative to pin 15 (GND), Basic Insulation.

Note 2: Decrease due to higher ambient temperature.

## ELECTRICAL PARAMETERS (Ta=25°C and VCC=5V, unless otherwise specified)

Parameter	Symbol	Conditions	Min.	Тур.	Max.	Unit
Power Supply	Vcc	-	4.5	5	5.5	V
Supply Current	Icc	OUT pin floated	-	20	25	mA
Internal benchmark	VZCR		2.470	2.500	2.530	V
Zero Current Output Voltage	V <sub>OUT(Q)</sub>	IP=0	2.490	2.500	2.510	V
Output Capacitance Load	CL		-	-	1	nF
Output Resistive Load	R∟		1.5	-	-	kΩ
Resistance of Primary Conductor	R₽		-	0.45	-	mΩ
Propagation Time	t <sub>D</sub>			1	2	us
Rise Time	tr		-	1	2.2	us
Common Mode Rejection Ratio	CMRR		38	-	-	dB
Bandwidth	BW	-3dB	250	-	-	kHz
Reference Output Source Current	I <sub>ZCR(SOURCE)</sub>		-	-	400	uA



## crossMAG series

Continued:								
Reference Output Sink Current	I <sub>ZCR(SINK)</sub>		-	-	2000	uA		
Nonlinearity	Lin <sub>ERR</sub>		-	0.2	0.5	%		
Symmetry	Symerr		-	0.8	1.5	%		
Power-on Time	T <sub>POR</sub>	Output rising from 0 to 90% of steady-state	-	10	-	us		

## **5A PERFORMANCE CHARACTERISTICS**

Parameter	Symbol	Conditions	Min.	Тур.	Max.	Unit
Current Accuracy Range	I <sub>P</sub>	-	-5	-	5	А
Sensitivity	Sens	full range of I <sub>P</sub>	388	400	412	mV/A
Zero Current Differential Output Error	V <sub>OE</sub>		-40		40	mV
Noise	V <sub>NOISE(RMS)</sub>		-	65	-	mV
Zero Current Output Slope	$\Delta V_{OUT(Q)}$		-	0.34	-	mV/°C
Sensitivity Slope	Δsens		-	0.096	-	mV/A/°C
Total Output Error	Етот		-3.0	-	3.0	%

## **10A PERFORMANCE CHARACTERISTICS**

Parameter	Symbol	Conditions	Min.	Тур.	Max.	Unit
Current Accuracy Range	I <sub>P</sub>	-	-10	-	10	Α
Sensitivity	Sens	full range of I <sub>P</sub>	194	200	206	mV/A
Zero Current Differential Output Error	V <sub>OE</sub>		-35		35	mV
Noise	V <sub>NOISE(RMS)</sub>		-	33	-	mV
Zero Current Output Slope	$\Delta V_{OUT(Q)}$		-	0.34	-	mV/°C
Sensitivity Slope	$\Delta_{SENS}$		-	0.048	-	mV/A/°C
Total Output Error	Етот		-3.0	-	3.0	%

## **20A PERFORMANCE CHARACTERISTICS**

Parameter	Symbol	Conditions	Min.	Тур.	Max.	Unit
i didilictei	Cyllibol	Conditions	IVIIII.	Typ.	Wax.	Offic
Current Accuracy Range	l <sub>P</sub>	-	-20	-	20	Α
Sensitivity	Sens	full range of I <sub>P</sub>	97	100	103	mV/A
Zero Current Differential Output Error	VoE		-40		40	mV
Noise	V <sub>NOISE(RMS)</sub>		-	16	-	mV
Zero Current Output Slope	$\Delta V_{OUT(Q)}$		-	0.34	-	mV/°C
Sensitivity Slope	$\Delta_{SENS}$		-	0.024	-	mV/A /°C
Total Output Error	Етот		-3.0	-	3.0	%



## **25A PERFORMANCE CHARACTERISTICS**

Parameter	Symbol	Conditions	Min.	Тур.	Max.	Unit
Current Accuracy Range	l <sub>P</sub>	-	-25	-	25	Α
Sensitivity	Sens	full range of I <sub>P</sub>	77.6	80	82.4	mV/A
Zero Current Differential Output Error	V <sub>OE</sub>		-35		35	mV
Noise	V <sub>NOISE(RMS)</sub>		-	13	-	mV
Zero Current Output Slope	$\Delta V_{\text{OUT(Q)}}$		-	0.34	-	mV/°C
Sensitivity Slope	Δsens		-	0.019	-	mV/A /°C
Total Output Error	Етот		-3.0	-	3.0	%

#### **30A PERFORMANCE CHARACTERISTICS**

Parameter	Symbol	Conditions	Min.	Тур.	Max.	Unit
Current Accuracy Range	l <sub>P</sub>	-	-30	-	30	Α
Sensitivity	Sens	full range of I <sub>P</sub>	64.7	66.7	68.7	mV/A
Zero Current Differential Output Error	V <sub>OE</sub>		-30		30	mV
Noise	V <sub>NOISE(RMS)</sub>		-	11	-	mV
Zero Current Output Slope	$\Delta V_{OUT(Q)}$		-	0.34	-	mV/°C
Sensitivity Slope	Δsens		-	0.016	-	mV/A /°C
Total Output Error	Етот		-3.0	-	3.0	%

#### **40A PERFORMANCE CHARACTERISTICS**

Parameter	Symbol	Conditions	Min.	Тур.	Max.	Unit
Current Accuracy Range	I <sub>P</sub>	-	-40	-	40	Α
Sensitivity	Sens	full range of I <sub>P</sub>	48.5	50	51.5	mV/A
Zero Current Differential Output Error	Voe		-25		25	mV
Noise	V <sub>NOISE(RMS)</sub>		-	10	-	mV
Zero Current Output Slope	$\Delta V_{OUT(Q)}$		-	0.34	-	mV/°C
Sensitivity Slope	Δsens		-	0.012	-	mV/A /°C
Total Output Error	Етот		-3.0	-	3.0	%

#### **50A PERFORMANCE CHARACTERISTICS**

OCAT EN CHIMANGE CHARACTERICITICS						
Parameter	Symbol	Conditions	Min.	Тур.	Max.	Unit
Current Accuracy Range	I <sub>P</sub>	-	-50	-	50	Α
Sensitivity	Sens	full range of I <sub>P</sub>	38.8	40	41.2	mV/A
Zero Current Differential Output Error	V <sub>OE</sub>		-20		20	mV
Noise	V <sub>NOISE(RMS)</sub>		-	10	-	mV
Zero Current Output Slope	$\Delta V_{OUT(Q)}$		-	0.34	-	mV/°C
Sensitivity Slope	Δsens		-	0.010	-	mV/A /°C
Total Output Error	Етот		-3.0	-	3.0	%



## **65A PERFORMANCE CHARACTERISTICS**

Parameter	Symbol	Conditions	Min.	Тур.	Max.	Unit
Current Accuracy Range	l <sub>P</sub>	-	-65	-	65	Α
Sensitivity	Sens	full range of I <sub>P</sub>	29.8	30.8	31.7	mV/A
Zero Current Differential Output Error	V <sub>OE</sub>		-15		15	mV
Noise	V <sub>NOISE(RMS)</sub>		-	10	-	mV
Zero Current Output Slope	$\Delta V_{\text{OUT(Q)}}$		-	0.34	-	mV/°C
Sensitivity Slope	Δsens		-	0.007	-	mV/A /°C
Total Output Error	Етот		-3.0	-	3.0	%

NOTE: The following series exceeding 65A range cannot be powered continuously. Besides, the average current I<sub>RMS</sub> can only be made ≤ 65A with duty cycle (%)

#### **75A PERFORMANCE CHARACTERISTICS**


Parameter	Symbol	Conditions	Min.	Тур.	Max.	Unit
Current Accuracy Range	I <sub>P</sub>	-	-75	-	75	Α
Sensitivity	Sens	full range of I <sub>P</sub>	25.9	26.7	27.5	mV/A
Zero Current Differential Output Error	V <sub>OE</sub>		-15		15	mV
Noise	V <sub>NOISE(RMS)</sub>		-	10	-	mV
Zero Current Output Slope	$\Delta V_{\text{OUT(Q)}}$		-	0.34	-	mV/°C
Sensitivity Slope	Δsens		-	0.006	-	mV/A /°C
Total Output Error	Етот		-3.0	-	3.0	%

## **100A PERFORMANCE CHARACTERISTICS**


Parameter	Symbol	Conditions	Min.	Тур.	Max.	Unit
Current Accuracy Range	I <sub>P</sub>	-	-100	-	100	Α
Sensitivity	Sens	full range of I <sub>P</sub>	19.4	20	20.6	mV/A
Zero Current Differential Output Error	V <sub>OE</sub>		-15		15	mV
Noise	V <sub>NOISE(RMS)</sub>		-	10	-	mV
Zero Current Output Slope	$\Delta V_{OUT(Q)}$		-	0.34	-	mV/°C
Sensitivity Slope	$\Delta_{SENS}$		-	0.005	-	mV/A /°C
Total Output Error	Етот		-3.0	-	3.0	%




#### TYPICAL APPLICATION CIRCUITS




Typical Output Application




Signal Attenuation Circuit




Peak Current Detection



Over Current Fault Latch




Rectifier output, instead of current transformer application




Zero Migration Application

# crosschip



Application of single source zero shift with unidirectional current

Note: the output current of IzcR is < 0.4mA. It is suggested that 0.3mA



Gain amplifier application

Note: output direction of Vout



#### **Function Description**

The CC6921 device is a precision current sensor based on Hall sensor. It has  $1000V_{RMS}$  basic isolated working voltage, less than 3% full scale error and zero current reference signal output in the whole temperature range, which can realize unidirectional or bidirectional current detection. The input current flows through a wire between isolated input current pins, which has a resistance of  $0.45 \text{ m}\Omega$  at room temperature to reduce insertion loss. The magnetic field generated by the input current is sensed by Hall sensor and amplified by precise signal chain. It can be used for AC and DC current measurement with a bandwidth of 250kHz. The measuring current is  $5A\sim100A$ . There are 10 kinds of Current sensing range to choose. It can work under single power supply of 4.5V to 5.5V. CC6921 is optimized for high accuracy and temperature stability, compensating for misalignment and sensitivity over the entire range.

The input current of CC6921 flows through the primary side of the package through IP + and IP - pins. The current flowing through the chip generates a magnetic field proportional to the input current and is measured by an isolated Precision Hall sensor IC. Compared with other current measurement methods, the low impedance lead frame path reduces power consumption and does not require any external devices on the primary side. In addition, the internal integrated differential common mode suppression circuit can make the chip output not affected by external interference magnetic signal, and only measure the magnetic field generated by the input current, so as to suppress the interference of external magnetic field.

The typical resistance of the primary current input conductor at 25 ° C is 0.45 m $\Omega$ . The lead frame is made of copper. The temperature coefficient of the input wire is positive, and the wire resistance increases with the increase of temperature. The typical temperature coefficient is 3300 ppm/°C. For every 100 ° C increase in temperature, the primary side resistance will increase by 33%.

#### **Input Current**

In use, the primary side of the chip (package pins 1-8) is connected in series at any position in the whole circuit. The input current flowing from IP + (package pins 1-4) to IP - (package pins 5-8) is positive, otherwise it is negative. Do not shunt resistors between IP + and IP -, unless there are very special reasons - such as minimizing insertion loss - which will reduce the current flowing through the chip, and the wire resistance will also be affected by temperature drift, which requires external temperature and precision correction of the whole system.

### **Output Characteristic**

The static output point (IP = 0A) of CC6921 is VCC / 2.

When the current increases, the  $V_{OUT}$  increases until the saturation voltage of the output operational amplifier (VCC – rail voltage); when the current decreases, the  $V_{OUT}$  decreases until the saturation voltage (GND + rail voltage) of the Output Op Amp. Crosschip ensures the accuracy and linearity of  $V_{OUT}$  in the range of  $0.5 \sim 4.5$ V. In order to ensure the consistency of mass manufacturing, there is a certain margin in this range, but it is not recommended for customers to use this margin.

When the input current exceeds the range, the output of VouT is close to the rail voltage of the power supply. When the input current does not exceed the tolerance limit of the chip, the voltage will always be maintained. After the input current returns to the range, the output of VouT will return to normal without any damage to the chip.




Product Name	Input Current	Sensitivity(mV/A)	Calculation Formula (Note 1)
CC6921SO-5A	-5A ~ +5A	400	V <sub>OUT</sub> = VCC / 2 + 0.4 × I <sub>P</sub> (A)(V)
CC6921SO-10A	-10A ~ +10A	200	V <sub>OUT</sub> = VCC / 2 + 0.2 × I <sub>P</sub> (A)(V)
CC6921SO-20A	-20A ~ +20A	100	V <sub>OUT</sub> = VCC / 2 + 0.1× I <sub>P</sub> (A)(V)
CC6921SO-25A	-25A ~ +25A	80	V <sub>OUT</sub> = VCC / 2 + 0.08× I <sub>P</sub> (A)(V)
CC6921SO-30A	-30A ~ +30A	66.7	V <sub>OUT</sub> = VCC / 2 + 0.0667 × I <sub>P</sub> (A)(V)
CC6921SO-40A	-40A ~ +40A	50	V <sub>OUT</sub> = VCC / 2 +0.05× I <sub>P</sub> (A)(V)
CC6921SO-50A	-50A ~ +50A	40	V <sub>OUT</sub> = VCC / 2 +0.04 × I <sub>P</sub> (A)(V)
CC6921SO-65A	-65A ~ +65A	30.8	V <sub>OUT</sub> = VCC / 2 + 0.0308 × I <sub>P</sub> (A)(V)
CC6921SO-75A	-75A ~ +75A	26.7	V <sub>OUT</sub> = VCC / 2 + 0.0267 × I <sub>P</sub> (A)(V)
CC6921SO-100A	-100A ~ +100A	20	V <sub>OUT</sub> = VCC / 2 + 0.02 × I <sub>P</sub> (A)(V)

**Note**: the formula is only applicable to DC current calculation. When AC current is applied, pay attention to  $I_{PEAK} = 1.414 \times I_{RMS}$  and the positive & negative current direction.




### Relationship between Package Temperature & Input Current




Input Current (IP) vs. Package temperature

**Note:** Based on the demo board test, for specific applications, it is necessary to strengthen the heat dissipation according to the actual application scenario or select the board with high Tg.


For example: Temperature tests shall be considered for the specific installation conditions in end system which needs a cooling system that can provide wind speeds of at least 13.8 m/s.



Package Thermography (Input Current 30A)




Package Thermography (Input Current 50A)




Thickness: 1.6mm, FR-4 double-sided plate, 4oz copper foil total 10000m2

Test environment: open environment, stagnant air





Package Thermography (Input Current 40A)




Package Thermography (Input Current 65A)









Icc vs. Ta




AC output voltage waveform (50Hz)



AC output voltage waveform (50kHz)





AC output voltage waveform (100kHz)



AC output voltage waveform (250kHz)









Vout vs IP (20A)

(Positive Current Rising Edge Response)

Vour vs IP (20A)

(Negative Current Rising Edge Response)






Vour vs IP (20A)


(Positive Current Falling Edge Response)

Vour vs IP (20A)

(Negative Current Falling Edge Response)









Vout vs IP (30A)

(Positive Current Rising Edge Response)

Vout vs IP (30A)

(Negative Current Rising Edge Response)






Vour vs IP (30A)


(Positive Current Falling Edge Response)

Vour vs IP (30A)

(Negative Current Falling Edge Response)









Vout vs IP (40A)

(Positive Current Rising Edge Response)

Vout vs IP (40A)

(Negative Current Rising Edge Response)





Vour vs IP (40A)


(Positive Current Falling Edge Response)


Vour vs IP (40A)

(Negative Current Falling Edge Response)





#### 20A Series







 $V_{\text{OUTQ}}$  vs. Ta  $V_{\text{ZCR}}$  vs. Ta





V<sub>OE</sub> vs. Ta Sens error vs. Ta







V<sub>OUT</sub> error vs. Ta V<sub>OUT</sub> vs. IP





## **30A Series**







Voutq vs. Ta Vzcr vs. Ta





V<sub>OE</sub> vs. Ta Sens error vs. Ta







 $V_{\text{OUT}}$  error vs. Ta  $V_{\text{OUT}}$  vs. IP





#### **40A Series**







Voutq vs. Ta Vzcr vs. Ta





V<sub>OE</sub> vs. Ta Sens error vs. Ta






 $V_{\text{OUT}}$  error vs. Ta  $V_{\text{OUT}}$  vs. IP



□ .004[0.1]|Z


## **PACKAGE INFORMATION**

#### **SOP16W PACKAGE**



- 16X b [♠].01[0.25]@|Z|U\$|T\$]

Symbol	Millimeters					
Syllibol	Min	TYP	Max			
Α	2.35		2.65			
A1	0.10		0.30			
b	0.33		0.51			
С	0.23		0.32			
D	10.10		10.50			
E1	7.40		7.60			
E	10.00		10.63			
е	1.27 BSC					
L	0.40		1.27			
h	0.25		0.75			
θ	0°		8°			



#### Note:

1. All dimensions are in millimeters.

#### Marking:

1<sup>st</sup> Line: CC6921SO 2<sup>nd</sup> Line: ELC– XXA


XX—I<sub>P</sub> Range 3<sup>rd</sup> Line: XXYYWW XX –assembler code

YY – assembly year (last 2 digits)

WW - assembly week number



## Package Reference



Reference: shorten pad length and increase creepage distance



## CrossChip

CrossChip Microsystems Inc. was founded in 2013, is a national high-tech enterprise, engaged in integrated circuit design and sales. The company has strong technical strength, has more than 50 kinds of patents, mainly used in Hall sensor signal processing, with the following product lines:

- ✓ High precision linear Hall sensor
- ✓ All kinds of Hall switches
- ✓ Single phase motor drive
- ✓ Single chip current sensor
- ✓ AMR Magnetoresistance sensor

#### Contact us

#### Chengdu

Address: 4th floor, unit 2, building 3, No. 88, Tianchen Road, Gaoxinxi Zone, Chengdu, Sichuan Province

Tel: + 86 - 28 - 87787685

Email: support@crosschipmicro.com

Website: http://www.crosschipmicro.com

#### Shenzhen

Address: 605 room, 6F, Beike building, NO.18 Keyuan Rd, Yuehai Street, Nanshan District, Shenzhen

#### Shanghai

Address: Makeblock, 3 / F, magic square community, 4476 Huyi Road, Jiading District, Shanghai