

CC6924

5000V isolation voltage resistance, 25kA surge current
High-performance Hall-effect current sensor of 20A-200A

FEATURES

- ◆ Built-in VREF Output, External VREF Input:
 - Built-in VREF Output: V_{OE} is programmable to < 5mV
 - External VREF Input: V_{OUT} quiescent output voltage is consistent with it
- ◆ Measuring current range: 20A, 30A, 40A, 50A, 65A, 75A, 80A, 100A, 125A, 150A, 200A
- ◆ Low noise, Single-end analog output
- ◆ High isolation and withstand voltage (5000V_{RMS} isolation voltage between pins 1-8 and 9-16)
- ◆ $V_{WBI}=1500V_{RMS}$; $V_{WRI}=750V_{RMS}$
- ◆ Less power loss, internal conductor's resistance is 0.3mΩ
- ◆ High bandwidth, up to 250kHz, 1.2μs output rise time in response to step input current
- ◆ Room temperature error ±1%, sensitivity temperature drift up to ±2.5%.
- ◆ Good temperature stability, using Hall signal amplification circuit and temperature compensation circuit
- ◆ Differential Hall structure, strong resistance to external magnetic interference
- ◆ Strong resistance to mechanical stress, magnetic parameters will not be offset by external pressure
- ◆ ESD (HBM) 6kV, ESD(CDM) 2kV, LU 500mA

APPLICATIONS

- ◆ Motor controller
- ◆ Load detection and management
- ◆ Switch-mode power supplies
- ◆ Over-current fault protection
- ◆ PV inverter
- ◆ New energy



Certificate Number:
TUV MARK: R 50590288



Certificate Number:
E526186-A6002-UL

GENERAL DESCRIPTION

The CC6924 device is a high-performance Hall-effect current sensor that can measure DC or AC current more efficiently, and has the advantages of high accuracy, excellent linearity and temperature stability in industrial, consumer, and communication equipment.


The CC6924 device consists of a high-precision, low-noise linear Hall integrated circuit and a low-resistance main current conductor. Internal copper conductor's resistance is typical 0.3mΩ, which provides much less power loss than the universal resistor sampling method. Otherwise, its internal inherent insulation provides 5000V_{RMS} (AC) insulation withstand voltage between the input current path and the secondary circuit. The sensor adopts linear Hall sensor temperature compensation technology, which has high temperature stability characteristics.

The differential common-mode suppression circuit integrated in CC6924 can make the chip output unaffected by external interference magnetic signals. The integrated dynamic offset elimination circuit makes the sensitivity of the chip independent of external stress and chip packaging stress.



CC6924 is available in SOP16W package. It's operating ambient temperature range is -40~125°C. Comply with RoHS requirements.

DEVICE INFORMATION

Part Number	Package	Body Size (TYP.)
CC6924	SOP16W	10.30mm×7.50mm



PRODUCT PACKAGE PICTURE


TYPICAL APPLICATION

FUNCTION BLOCK DIAGRAM


ORDERING INFORMATION

Part No.	SENS. (mV/A)	Package	Packing Form
CC6924SG-5FB020	100	SOP16W	tape reel, 1000 pcs/reel
CC6924SG-5FB030	66.67	SOP16W	tape reel, 1000 pcs/reel
CC6924SG-5FB040	50	SOP16W	tape reel, 1000 pcs/reel
CC6924SG-5FB050	40	SOP16W	tape reel, 1000 pcs/reel
CC6924SG-5FB065	30.77	SOP16W	tape reel, 1000 pcs/reel
CC6924SG-5FB075	26.67	SOP16W	tape reel, 1000 pcs/reel
CC6924SG-5FB080	25	SOP16W	tape reel, 1000 pcs/reel
CC6924SG-5FB100	20	SOP16W	tape reel, 1000 pcs/reel
CC6924SG-5FB125	16	SOP16W	tape reel, 1000 pcs/reel
CC6924SG-5FB150	13.33	SOP16W	tape reel, 1000 pcs/reel
CC6924SG-5FB200	10	SOP16W	tape reel, 1000 pcs/reel
CC6924SG-3FB020	66	SOP16W	tape reel, 1000 pcs/reel
CC6924SG-3FB030	44	SOP16W	tape reel, 1000 pcs/reel
CC6924SG-3FB040	33	SOP16W	tape reel, 1000 pcs/reel
CC6924SG-3FB050	26.4	SOP16W	tape reel, 1000 pcs/reel
CC6924SG-3FB065	20.31	SOP16W	tape reel, 1000 pcs/reel
CC6924SG-3FB075	17.6	SOP16W	tape reel, 1000 pcs/reel
CC6924SG-3FB100	13.2	SOP16W	tape reel, 1000 pcs/reel
CC6924SG-3FB125	10.56	SOP16W	tape reel, 1000 pcs/reel
CC6924SG-3FB150	8.8	SOP16W	tape reel, 1000 pcs/reel
CC6924SG-XXX (Note1)	-	SOP16W	tape reel, 1000 pcs/reel

Note 1: When XXX is within the range of 200A, it can be customized according to customer needs.

PRODUCTION NAME DEFINITION



CrossChip Part Number: Fixed to CC

Main Device Name: Main material number name

Package Part Number: Package code

Supply Voltage: Fixed operational voltage , 3 - VCC=3.3V; 5 - VCC=5V


Output Type and Directionality: Output type and polarity

Output type: F: Fixed output

Output direction: B: Bidirectional

Current Range : Measure the range of the current

PINOUT DIAGRAM



SOP16W Package

Name	Number	Description	Name	Number	Description
IP+	1	Current Sampled +	NC	9	hang in the air
IP+	2	Current Sampled +	VCC	10	Supply Voltage
IP+	3	Current Sampled +	NC	11	hang in the air
IP+	4	Current Sampled +	VOUT	12	Analog Voltage Output
IP-	5	Current Sampled -	VREF	13	Zero Current Reference Signal Output
IP-	6	Current Sampled -	NC	14	hang in the air
IP-	7	Current Sampled -	GND	15	Ground
IP-	8	Current Sampled -	NC	16	hang in the air

ABSOLUTE MAXIMUM RATINGS

Parameter	Symbol	Value	Unit
Power Supply	V_{CC}	6.5	V
Output Voltage	V_{OUT}, V_{REF}	-0.3~VCC+0.3	V
Input Current Peak Current (3 s)	I_{PEAK}	200	A
Input Current Continuous Current	I_{CON}	72	A
Operating Ambient Temperature	T_A	-40~125	°C
Junction Temperature	T_J	165	°C
Storage Temperature	T_S	-55~150	°C
Moisture Sensitivity Level	MSL	3	
Electrostatic Discharge Voltage	ESD(HBM)	6	kV
	ESD(CDM)	2	kV
Latch Up	LU	500	mA

Note: Stresses beyond those listed under *Absolute Maximum Ratings* may cause permanent damage to the device. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

ISOLATION CHARACTERISTICS


Parameter	Symbol	Test Conditions	Value	Unit
Distance Through Insulation	DTI	Minimum internal distance through insulation	127	um
Comparative Tracking Index	CTI		≥600	V
Withstand Isolation Voltage	V _{ISO}	50/60Hz, 1min	5000	V _{RMS}
		t = 1s	6000	
Working Voltage for Basic Insulation	V _{WVBI}	Basic insulation TUV mark: EN IEC 62368-1:2020+A11:2020	2121	V _{PK} or V _{DC}
		UL 62368-1, 3rd Ed, 2021-10-22	1500	V _{RMS}
		CB Scheme: IEC 62368-1: 2018		
Working Voltage for Reinforced Insulation	V _{WVRI}	Reinforced insulation TUV mark: EN IEC 62368-1:2020+A11:2020	1060	V _{PK} or V _{DC}
		UL 62368-1, 3rd Ed, 2021-10-22	750	V _{RMS}
		CB Scheme: IEC 62368-1: 2018		
Clearance	D _{cl}	minimum distance through air from IP leads to signal leads	8.3	mm
Creepage	D _{cr}	minimum distance from the IP wire to the signal wire along the package	8.3	mm
Maximum Surge Isolation Voltage	V _{IOSM}	IEC 61000-4-5 Tested in air, ± 5 pulses, 2 times/min 1.2us (rise) / 50us (width)	11	kV
Surge Current	I _{SURGE}	IEC 61000-4-5 Tested in air, ± 5 pulses, 1 times/min 8μs (rise) / 20μs (width)	25	kA

THERMAL RESISTANCE INFORMATION

Parameter	Symbol, Conditions	value	Unit
Junction-to-ambient	θ _{JA} (SOP16W)	78	°C/W
Junction-to-case	θ _{JC} (SOP16W)	24	°C/W

ELECTRICAL PARAMETERS (V_{CC}=5V/3.3V, C_{OUT}=1nF, C_{REF}=1nF, TA=25°C, unless otherwise specified)

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Supply Section, VCC=5V						
Power Supply	V _{CC}		4.5	5	5.5	V
Undervoltage Protection Release Threshold	UV	V _{CC} > UV, Undervoltage protection release		4.15		V
Undervoltage Protection Hysteresis Voltage	UV _{HYS}	V _{CC} < UV - UV _{HYS} , Lock the chip		0.2		V
Supply Current	I _{CC}		18	22	28	mA
Power-on Time	t _{POR}			22		us



Continued:

Supply Section, VCC=3.3V						
Power Supply	V _{CC}		3	3.3	3.6	V
Undervoltage Protection Release Threshold	UV	V _{CC} > UV, Undervoltage protection release		2.8		V
Undervoltage Protection Hysteresis Voltage	UV _{HYS}	V _{CC} < UV - UV _{HYS} , Lock the chip		0.1		V
Supply Current	I _{CC}		16	19	25	mA
Power-on Time	t _{POR}			22		us
Output Section, VOUT						
VOUT Filter Capacitors	C _{OUT}	VOUT to GND		1	2.2	nF
VOUT Load Resistance	R _{L_OUT}	VOUT to GND	4.7			kΩ
VOUT High Saturation Voltage	V _{SATH}	V _{SATH} = V _{CC} - V _{OUT} , R _L =10kΩ to GND		0.1	0.2	V
VOUT Low Saturation Voltage	V _{SATL}	V _{SATL} = V _{OUT} , R _L =10kΩ to VCC		0.1	0.2	V
VOUT Output Source Current	I _{OUT_SOURCE}	VOUT to GND short-circuit current		8		mA
VOUT Output Sink Current	I _{OUT_SINK}	VOUT to VCC short-circuit current		28		mA
Signal Chain -3dB Bandwidth	f _{-3dB}	Small signal -3dB bandwidth		250		kHz
Signal Response Time	t _{RES}	Input current up to 90% to VOUT 90%		1.2	2	us
Reference Section, VREF						
VREF Filter Capacitors	C _{REF}	VREF to GND		1	2.2	nF
VREF Load Resistance	R _{L_REF}	VREF to GND	4.7			kΩ
VREF Output Voltage	V _{REF}	5V nominal supply voltage series	2.49	2.5	2.51	V
		3.3V nominal supply voltage series	1.64	1.65	1.66	V
VREF Input Voltage	V _{REFIN}	VREF Input voltage range	0.1×V _{CC}		0.9×V _{CC}	V
VREF Output Source Current	I _{REF_SOURCE}	VREF to GND short-circuit current		2.8		mA
VREF Output Sink Current	I _{REF_SINK}	VREF to VCC short-circuit current		6		mA
On-resistance						
Primary on-resistance	R _P	T _A =25°C, I _P =10A		0.3		mΩ
Time drift parameter part						
Sens Lifetime Drift	Sens_drift	After the reliability test, test @ T _A =25°C	-1.5		1.5	%
V _{REF} Lifetime Drift	V _{REF_drift}	After the reliability test, test @ T _A =25°C	-12		12	mV
V _{OUT(Q)} Lifetime Drift	V _{OUT(Q)_drift}	After the reliability test, test @ T _A =25°C	-15		15	mV
V _{OE} Lifetime Drift	V _{OE_drift}	After the reliability test, test @ T _A =25°C	-8		8	mV

CC6924SG-5FB020 ($V_{CC}=5V$, $C_{OUT}=1nF$, $C_{REF}=1nF$, $T_A=25^\circ C$, unless otherwise specified)

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Current Accuracy Range	I_P	-	-20		20	A
Sensitivity	Sens	full range of I_P		100		mV/A
Zero Current Differential Output Error	V_{OE}	$V_{OE}=V_{OUT}-V_{REF}$, $I_P=0A$	-5		5	mV
Noise	$V_{N(RMS)}$	$I_P=0A$		15		mV
Zero Current Output Offset Drift	ΔV_{OE}	$T_A=-40^\circ C \sim 125^\circ C$ V_{OE} offset voltage drift = $V_{OE_TA} - V_{OE_25^\circ C}$	-20		20	mV
Zero Current Quiescent Output Voltage Temperature Drift	$\Delta V_{OUT(Q)}$	$T_A=-40^\circ C \sim 125^\circ C$ $V_{OUT(Q)}$ voltage drift = $V_{OUT(Q)_TA} - V_{OUT(Q)_25^\circ C}$	-25		25	mV
Sensitivity Error	Δ_{SENS}	$T_A=-40^\circ C \sim 125^\circ C$	-2.0		2.0	%
Total Output Error	E_{TOT}	$T_A=-40^\circ C \sim 125^\circ C$, $I_P=I_{P_MAX}$	-3.0		3.0	%
Linearity Error	LIN_{ERR}	$T_A=-40^\circ C \sim 125^\circ C$		0.2	0.4	%

CC6924SG-5FB030 ($V_{CC}=5V$, $C_{OUT}=1nF$, $C_{REF}=1nF$, $T_A=25^\circ C$, unless otherwise specified)

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Current Accuracy Range	I_P	-	-30		30	A
Sensitivity	Sens	full range of I_P		66.67		mV/A
Zero Current Differential Output Error	V_{OE}	$V_{OE}=V_{OUT}-V_{REF}$, $I_P=0A$	-5		5	mV
Noise	$V_{N(RMS)}$	$I_P=0A$		10		mV
Zero Current Output Offset Drift	ΔV_{OE}	$T_A=-40^\circ C \sim 125^\circ C$ V_{OE} offset voltage drift = $V_{OE_TA} - V_{OE_25^\circ C}$	-20		20	mV
Zero Current Quiescent Output Voltage Temperature Drift	$\Delta V_{OUT(Q)}$	$T_A=-40^\circ C \sim 125^\circ C$ $V_{OUT(Q)}$ voltage drift = $V_{OUT(Q)_TA} - V_{OUT(Q)_25^\circ C}$	-25		25	mV
Sensitivity Error	Δ_{SENS}	$T_A=-40^\circ C \sim 125^\circ C$	-2.5		2.5	%
Total Output Error	E_{TOT}	$T_A=-40^\circ C \sim 125^\circ C$, $I_P=I_{P_MAX}$	-3.0		3.0	%
Linearity Error	LIN_{ERR}	$T_A=-40^\circ C \sim 125^\circ C$		0.2	0.4	%

CC6924SG-5FB040 ($V_{CC}=5V$, $C_{OUT}=1nF$, $C_{REF}=1nF$, $T_A=25^\circ C$, unless otherwise specified)

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Current Accuracy Range	I_P	-	-40		40	A
Sensitivity	Sens	full range of I_P		50		mV/A
Zero Current Differential Output Error	V_{OE}	$V_{OE}=V_{OUT}-V_{REF}$, $I_P=0A$	-5		5	mV
Noise	$V_{N(RMS)}$	$I_P=0A$		7.5		mV
Zero Current Output Offset Drift	ΔV_{OE}	$T_A=-40^\circ C \sim 125^\circ C$ V_{OE} offset voltage drift = $V_{OE_TA} - V_{OE_25^\circ C}$	-20		20	mV
Zero Current Quiescent Output Voltage Temperature Drift	$\Delta V_{OUT(Q)}$	$T_A=-40^\circ C \sim 125^\circ C$ $V_{OUT(Q)}$ voltage drift = $V_{OUT(Q)_TA} - V_{OUT(Q)_25^\circ C}$	-25		25	mV
Sensitivity Error	Δ_{SENS}	$T_A=-40^\circ C \sim 125^\circ C$	-2.5		2.5	%
Total Output Error	E_{TOT}	$T_A=-40^\circ C \sim 125^\circ C$, $I_P=I_{P_MAX}$	-3.0		3.0	%
Linearity Error	LIN_{ERR}	$T_A=-40^\circ C \sim 125^\circ C$		0.2	0.4	%

CC6924SG-5FB050 ($V_{CC}=5V$, $C_{OUT}=1nF$, $C_{REF}=1nF$, $T_A=25^\circ C$, unless otherwise specified)

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Current Accuracy Range	I_P	-	-50		50	A
Sensitivity	Sens	full range of I_P		40		mV/A
Zero Current Differential Output Error	V_{OE}	$V_{OE}=V_{OUT}-V_{REF}$, $I_P=0A$	-5		5	mV
Noise	$V_{N(RMS)}$	$I_P=0A$		6		mV
Zero Current Output Offset Drift	ΔV_{OE}	$T_A=-40^\circ C \sim 125^\circ C$ V_{OE} offset voltage drift = $V_{OE_TA} - V_{OE_25^\circ C}$	-20		20	mV
Zero Current Quiescent Output Voltage Temperature Drift	$\Delta V_{OUT(Q)}$	$T_A=-40^\circ C \sim 125^\circ C$ $V_{OUT(Q)}$ voltage drift = $V_{OUT(Q)_TA} - V_{OUT(Q)_25^\circ C}$	-25		25	mV
Sensitivity Error	Δ_{SENS}	$T_A=-40^\circ C \sim 125^\circ C$	-2.5		2.5	%
Total Output Error	E_{TOT}	$T_A=-40^\circ C \sim 125^\circ C$, $I_P=I_{P_MAX}$	-3.0		3.0	%
Linearity Error	LIN_{ERR}	$T_A=-40^\circ C \sim 125^\circ C$		0.2	0.4	%

CC6924SG-5FB065 ($V_{CC}=5V$, $C_{OUT}=1nF$, $C_{REF}=1nF$, $T_A=25^\circ C$, unless otherwise specified)

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Current Accuracy Range	I_P	-	-65		65	A
Sensitivity	Sens	full range of I_P		30.77		mV/A
Zero Current Differential Output Error	V_{OE}	$V_{OE}=V_{OUT}-V_{REF}$, $I_P=0A$	-5		5	mV
Noise	$V_{N(RMS)}$	$I_P=0A$		4.75		mV
Zero Current Output Offset Drift	ΔV_{OE}	$T_A=-40^\circ C \sim 125^\circ C$ V_{OE} offset voltage drift = $V_{OE_TA} - V_{OE_25^\circ C}$	-20		20	mV
Zero Current Quiescent Output Voltage Temperature Drift	$\Delta V_{OUT(Q)}$	$T_A=-40^\circ C \sim 125^\circ C$ $V_{OUT(Q)}$ voltage drift = $V_{OUT(Q)_TA} - V_{OUT(Q)_25^\circ C}$	-25		25	mV
Sensitivity Error	Δ_{SENS}	$T_A=-40^\circ C \sim 125^\circ C$	-2.5		2.5	%
Total Output Error	E_{TOT}	$T_A=-40^\circ C \sim 125^\circ C$, $I_P=I_{P_MAX}$	-3.0		3.0	%
Linearity Error	LIN_{ERR}	$T_A=-40^\circ C \sim 125^\circ C$		0.2	0.4	%

CC6924SG-5FB075 ($V_{CC}=5V$, $C_{OUT}=1nF$, $C_{REF}=1nF$, $T_A=25^\circ C$, unless otherwise specified)

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Current Accuracy Range	I_P	-	-75		75	A
Sensitivity	Sens	full range of I_P		26.67		mV/A
Zero Current Differential Output Error	V_{OE}	$V_{OE}=V_{OUT}-V_{REF}$, $I_P=0A$	-5		5	mV
Noise	$V_{N(RMS)}$	$I_P=0A$		4		mV
Zero Current Output Offset Drift	ΔV_{OE}	$T_A=-40^\circ C \sim 125^\circ C$ V_{OE} offset voltage drift = $V_{OE_TA} - V_{OE_25^\circ C}$	-20		20	mV
Zero Current Quiescent Output Voltage Temperature Drift	$\Delta V_{OUT(Q)}$	$T_A=-40^\circ C \sim 125^\circ C$ $V_{OUT(Q)}$ voltage drift = $V_{OUT(Q)_TA} - V_{OUT(Q)_25^\circ C}$	-25		25	mV
Sensitivity Error	Δ_{SENS}	$T_A=-40^\circ C \sim 125^\circ C$	-2.5		2.5	%
Total Output Error	E_{TOT}	$T_A=-40^\circ C \sim 125^\circ C$, $I_P=I_{P_MAX}$	-3.0		3.0	%
Linearity Error	LIN_{ERR}	$T_A=-40^\circ C \sim 125^\circ C$		0.2	0.4	%

CC6924SG-5FB080 ($V_{CC}=5V$, $C_{OUT}=1nF$, $C_{REF}=1nF$, $T_A=25^\circ C$, unless otherwise specified)

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Current Accuracy Range	I_P	-	-80		80	A
Sensitivity	Sens	full range of I_P		25		mV/A
Zero Current Differential Output Error	V_{OE}	$V_{OE}=V_{OUT}-V_{REF}$, $I_P=0A$	-5		5	mV
Noise	$V_{N(RMS)}$	$I_P=0A$		3.75		mV
Zero Current Output Offset Drift	ΔV_{OE}	$T_A=-40^\circ C \sim 125^\circ C$ V_{OE} offset voltage drift = $V_{OE_TA} - V_{OE_25^\circ C}$	-20		20	mV
Zero Current Quiescent Output Voltage Temperature Drift	$\Delta V_{OUT(Q)}$	$T_A=-40^\circ C \sim 125^\circ C$ $V_{OUT(Q)}$ voltage drift = $V_{OUT(Q)_TA} - V_{OUT(Q)_25^\circ C}$	-25		25	mV
Sensitivity Error	Δ_{SENS}	$T_A=-40^\circ C \sim 125^\circ C$	-2.5		2.5	%
Total Output Error	E_{TOT}	$T_A=-40^\circ C \sim 125^\circ C$, $I_P=I_{P_MAX}$	-3.0		3.0	%
Linearity Error	LIN_{ERR}	$T_A=-40^\circ C \sim 125^\circ C$		0.2	0.4	%

CC6924SG-5FB100 ($V_{CC}=5V$, $C_{OUT}=1nF$, $C_{REF}=1nF$, $T_A=25^\circ C$, unless otherwise specified)

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Current Accuracy Range	I_P	-	-100		100	A
Sensitivity	Sens	full range of I_P		20		mV/A
Zero Current Differential Output Error	V_{OE}	$V_{OE}=V_{OUT}-V_{REF}$, $I_P=0A$	-5		5	mV
Noise	$V_{N(RMS)}$	$I_P=0A$		3		mV
Zero Current Output Offset Drift	ΔV_{OE}	$T_A=-40^\circ C \sim 125^\circ C$ V_{OE} offset voltage drift = $V_{OE_TA} - V_{OE_25^\circ C}$	-20		20	mV
Zero Current Quiescent Output Voltage Temperature Drift	$\Delta V_{OUT(Q)}$	$T_A=-40^\circ C \sim 125^\circ C$ $V_{OUT(Q)}$ voltage drift = $V_{OUT(Q)_TA} - V_{OUT(Q)_25^\circ C}$	-25		25	mV
Sensitivity Error	Δ_{SENS}	$T_A=-40^\circ C \sim 125^\circ C$	-2.5		2.5	%
Total Output Error	E_{TOT}	$T_A=-40^\circ C \sim 125^\circ C$, $I_P=I_{P_MAX}$	-3.0		3.0	%
Linearity Error	LIN_{ERR}	$T_A=-40^\circ C \sim 125^\circ C$		0.2	0.4	%

CC6924SG-5FB125 ($V_{CC}=5V$, $C_{OUT}=1nF$, $C_{REF}=1nF$, $T_A=25^\circ C$, unless otherwise specified)

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Current Accuracy Range	I_P	-	-125		125	A
Sensitivity	Sens	full range of I_P		16		mV/A
Zero Current Differential Output Error	V_{OE}	$V_{OE}=V_{OUT}-V_{REF}$, $I_P=0A$	-5		5	mV
Noise	$V_{N(RMS)}$	$I_P=0A$		2.5		mV
Zero Current Output Offset Drift	ΔV_{OE}	$T_A=-40^\circ C \sim 125^\circ C$ V_{OE} offset voltage drift = $V_{OE_TA} - V_{OE_25^\circ C}$	-20		20	mV
Zero Current Quiescent Output Voltage Temperature Drift	$\Delta V_{OUT(Q)}$	$T_A=-40^\circ C \sim 125^\circ C$ $V_{OUT(Q)}$ voltage drift = $V_{OUT(Q)_TA} - V_{OUT(Q)_25^\circ C}$	-25		25	mV
Sensitivity Error	Δ_{SENS}	$T_A=-40^\circ C \sim 125^\circ C$	-2.5		2.5	%
Total Output Error	E_{TOT}	$T_A=-40^\circ C \sim 125^\circ C$, $I_P=I_{P_MAX}$	-3.0		3.0	%
Linearity Error	LIN_{ERR}	$T_A=-40^\circ C \sim 125^\circ C$		0.2	0.4	%

CC6924SG-5FB150 ($V_{CC}=5V$, $C_{OUT}=1nF$, $C_{REF}=1nF$, $T_A=25^\circ C$, unless otherwise specified)

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Current Accuracy Range	I_P	-	-150		150	A
Sensitivity	Sens	full range of I_P		13.33		mV/A
Zero Current Differential Output Error	V_{OE}	$V_{OE}=V_{OUT}-V_{REF}$, $I_P=0A$	-5		5	mV
Noise	$V_{N(RMS)}$	$I_P=0A$		2		mV
Zero Current Output Offset Drift	ΔV_{OE}	$T_A=-40^\circ C \sim 125^\circ C$ V_{OE} offset voltage drift = $V_{OE_TA} - V_{OE_25^\circ C}$	-20		20	mV
Zero Current Quiescent Output Voltage Temperature Drift	$\Delta V_{OUT(Q)}$	$T_A=-40^\circ C \sim 125^\circ C$ $V_{OUT(Q)}$ voltage drift = $V_{OUT(Q)_TA} - V_{OUT(Q)_25^\circ C}$	-25		25	mV
Sensitivity Error	Δ_{SENS}	$T_A=-40^\circ C \sim 125^\circ C$	-2.5		2.5	%
Total Output Error	E_{TOT}	$T_A=-40^\circ C \sim 125^\circ C$, $I_P=I_{P_MAX}$	-3.0		3.0	%
Linearity Error	LIN_{ERR}	$T_A=-40^\circ C \sim 125^\circ C$		0.2	0.4	%

 CC6924SG-5FB200 ($V_{CC}=5V$, $C_{OUT}=1nF$, $C_{REF}=1nF$, $T_A=25^\circ C$, unless otherwise specified)

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Current Accuracy Range	I_P	-	-200		200	A
Sensitivity	Sens	full range of I_P		10		mV/A
Zero Current Differential Output Error	V_{OE}	$V_{OE}=V_{OUT}-V_{REF}$, $I_P=0A$	-5		5	mV
Noise	$V_{N(RMS)}$	$I_P=0A$		1.5		mV
Zero Current Output Offset Drift	ΔV_{OE}	$T_A=-40^\circ C \sim 125^\circ C$ V_{OE} offset voltage drift = $V_{OE_TA} - V_{OE_25^\circ C}$	-15		15	mV
Zero Current Quiescent Output Voltage Temperature Drift	$\Delta V_{OUT(Q)}$	$T_A=-40^\circ C \sim 125^\circ C$ $V_{OUT(Q)}$ voltage drift = $V_{OUT(Q)_TA} - V_{OUT(Q)_25^\circ C}$	-15		15	mV
Sensitivity Error	Δ_{SENS}	$T_A=-40^\circ C \sim 125^\circ C$	-2.5		2.5	%
Total Output Error	E_{TOT}	$T_A=-40^\circ C \sim 125^\circ C$, $I_P=I_{P_MAX}$	-3.0		3.0	%
Linearity Error	LIN_{ERR}	$T_A=-40^\circ C \sim 125^\circ C$		0.2	0.4	%

CC6924SG-3FB020 ($V_{CC}=3.3V$, $C_{OUT}=1nF$, $C_{REF}=1nF$, $T_A=25^{\circ}C$, unless otherwise specified)

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Current Accuracy Range	I_P	-	-20		20	A
Sensitivity	Sens	full range of I_P		66		mV/A
Zero Current Differential Output Error	V_{OE}	$V_{OE}=V_{OUT}-V_{REF}$, $I_P=0A$	-5		5	mV
Noise	$V_{N(RMS)}$	$I_P=0A$		15		mV
Zero Current Output Offset Drift	ΔV_{OE}	$T_A=-40^{\circ}C \sim 125^{\circ}C$ V_{OE} offset voltage drift = $V_{OE_TA} - V_{OE_25^{\circ}C}$	-20		20	mV
Zero Current Quiescent Output Voltage Temperature Drift	$\Delta V_{OUT(Q)}$	$T_A=-40^{\circ}C \sim 125^{\circ}C$ $V_{OUT(Q)}$ voltage drift = $V_{OUT(Q)_TA} - V_{OUT(Q)_25^{\circ}C}$	-25		25	mV
Sensitivity Error	Δ_{SENS}	$T_A=-40^{\circ}C \sim 125^{\circ}C$	-2.5		2.5	%
Total Output Error	E_{TOT}	$T_A=-40^{\circ}C \sim 125^{\circ}C$, $I_P=I_{P_MAX}$	-3.0		3.0	%
Linearity Error	LIN_{ERR}	$T_A=-40^{\circ}C \sim 125^{\circ}C$		0.2	0.4	%

CC6924SG-3FB030 ($V_{CC}=3.3V$, $C_{OUT}=1nF$, $C_{REF}=1nF$, $T_A=25^{\circ}C$, unless otherwise specified)

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Current Accuracy Range	I_P	-	-30		30	A
Sensitivity	Sens	full range of I_P		44		mV/A
Zero Current Differential Output Error	V_{OE}	$V_{OE}=V_{OUT}-V_{REF}$, $I_P=0A$	-5		5	mV
Noise	$V_{N(RMS)}$	$I_P=0A$		10		mV
Zero Current Output Offset Drift	ΔV_{OE}	$T_A=-40^{\circ}C \sim 125^{\circ}C$ V_{OE} offset voltage drift = $V_{OE_TA} - V_{OE_25^{\circ}C}$	-20		20	mV
Zero Current Quiescent Output Voltage Temperature Drift	$\Delta V_{OUT(Q)}$	$T_A=-40^{\circ}C \sim 125^{\circ}C$ $V_{OUT(Q)}$ voltage drift = $V_{OUT(Q)_TA} - V_{OUT(Q)_25^{\circ}C}$	-25		25	mV
Sensitivity Error	Δ_{SENS}	$T_A=-40^{\circ}C \sim 125^{\circ}C$	-2.5		2.5	%
Total Output Error	E_{TOT}	$T_A=-40^{\circ}C \sim 125^{\circ}C$, $I_P=I_{P_MAX}$	-3.0		3.0	%
Linearity Error	LIN_{ERR}	$T_A=-40^{\circ}C \sim 125^{\circ}C$		0.2	0.4	%

CC6924SG-3FB040 ($V_{CC}=3.3V$, $C_{OUT}=1nF$, $C_{REF}=1nF$, $T_A=25^{\circ}C$, unless otherwise specified)

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Current Accuracy Range	I_P	-	-40		40	A
Sensitivity	Sens	full range of I_P		33		mV/A
Zero Current Differential Output Error	V_{OE}	$V_{OE}=V_{OUT}-V_{REF}$, $I_P=0A$	-5		5	mV
Noise	$V_{N(RMS)}$	$I_P=0A$		7.5		mV
Zero Current Output Offset Drift	ΔV_{OE}	$T_A=-40^{\circ}C \sim 125^{\circ}C$ V_{OE} offset voltage drift = $V_{OE_TA} - V_{OE_25^{\circ}C}$	-20		20	mV
Zero Current Quiescent Output Voltage Temperature Drift	$\Delta V_{OUT(Q)}$	$T_A=-40^{\circ}C \sim 125^{\circ}C$ $V_{OUT(Q)}$ voltage drift = $V_{OUT(Q)_TA} - V_{OUT(Q)_25^{\circ}C}$	-25		25	mV
Sensitivity Error	Δ_{SENS}	$T_A=-40^{\circ}C \sim 125^{\circ}C$	-2.5		2.5	%
Total Output Error	E_{TOT}	$T_A=-40^{\circ}C \sim 125^{\circ}C$, $I_P=I_{P_MAX}$	-3.0		3.0	%
Linearity Error	LIN_{ERR}	$T_A=-40^{\circ}C \sim 125^{\circ}C$		0.2	0.4	%

CC6924SG-3FB050 ($V_{CC}=3.3V$, $C_{OUT}=1nF$, $C_{REF}=1nF$, $T_A=25^\circ C$, unless otherwise specified)

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Current Accuracy Range	I_P	-	-50		50	A
Sensitivity	Sens	full range of I_P		26.4		mV/A
Zero Current Differential Output Error	V_{OE}	$V_{OE}=V_{OUT}-V_{REF}$, $I_P=0A$	-5		5	mV
Noise	$V_{N(RMS)}$	$I_P=0A$		6		mV
Zero Current Output Offset Drift	ΔV_{OE}	$T_A=-40^\circ C \sim 125^\circ C$ V_{OE} offset voltage drift = $V_{OE_TA} - V_{OE_25^\circ C}$	-20		20	mV
Zero Current Quiescent Output Voltage Temperature Drift	$\Delta V_{OUT(Q)}$	$T_A=-40^\circ C \sim 125^\circ C$ $V_{OUT(Q)}$ voltage drift = $V_{OUT(Q)_TA} - V_{OUT(Q)_25^\circ C}$	-25		25	mV
Sensitivity Error	Δ_{SENS}	$T_A=-40^\circ C \sim 125^\circ C$	-2.5		2.5	%
Total Output Error	E_{TOT}	$T_A=-40^\circ C \sim 125^\circ C$, $I_P=I_{P_MAX}$	-3.0		3.0	%
Linearity Error	LIN_{ERR}	$T_A=-40^\circ C \sim 125^\circ C$		0.2	0.4	%

CC6924SG-3FB065 ($V_{CC}=3.3V$, $C_{OUT}=1nF$, $C_{REF}=1nF$, $T_A=25^\circ C$, unless otherwise specified)

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Current Accuracy Range	I_P	-	-65		65	A
Sensitivity	Sens	full range of I_P		20.31		mV/A
Zero Current Differential Output Error	V_{OE}	$V_{OE}=V_{OUT}-V_{REF}$, $I_P=0A$	-5		5	mV
Noise	$V_{N(RMS)}$	$I_P=0A$		4.75		mV
Zero Current Output Offset Drift	ΔV_{OE}	$T_A=-40^\circ C \sim 125^\circ C$ V_{OE} offset voltage drift = $V_{OE_TA} - V_{OE_25^\circ C}$	-20		20	mV
Zero Current Quiescent Output Voltage Temperature Drift	$\Delta V_{OUT(Q)}$	$T_A=-40^\circ C \sim 125^\circ C$ $V_{OUT(Q)}$ voltage drift = $V_{OUT(Q)_TA} - V_{OUT(Q)_25^\circ C}$	-25		25	mV
Sensitivity Error	Δ_{SENS}	$T_A=-40^\circ C \sim 125^\circ C$	-2.5		2.5	%
Total Output Error	E_{TOT}	$T_A=-40^\circ C \sim 125^\circ C$, $I_P=I_{P_MAX}$	-3.0		3.0	%
Linearity Error	LIN_{ERR}	$T_A=-40^\circ C \sim 125^\circ C$		0.2	0.4	%

CC6924SG-3FB075 ($V_{CC}=3.3V$, $C_{OUT}=1nF$, $C_{REF}=1nF$, $T_A=25^\circ C$, unless otherwise specified)

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Current Accuracy Range	I_P	-	-75		75	A
Sensitivity	Sens	full range of I_P		17.6		mV/A
Zero Current Differential Output Error	V_{OE}	$V_{OE}=V_{OUT}-V_{REF}$, $I_P=0A$	-5		5	mV
Noise	$V_{N(RMS)}$	$I_P=0A$		4		mV
Zero Current Output Offset Drift	ΔV_{OE}	$T_A=-40^\circ C \sim 125^\circ C$ V_{OE} offset voltage drift = $V_{OE_TA} - V_{OE_25^\circ C}$	-20		20	mV
Zero Current Quiescent Output Voltage Temperature Drift	$\Delta V_{OUT(Q)}$	$T_A=-40^\circ C \sim 125^\circ C$ $V_{OUT(Q)}$ voltage drift = $V_{OUT(Q)_TA} - V_{OUT(Q)_25^\circ C}$	-25		25	mV
Sensitivity Error	Δ_{SENS}	$T_A=-40^\circ C \sim 125^\circ C$	-2.5		2.5	%
Total Output Error	E_{TOT}	$T_A=-40^\circ C \sim 125^\circ C$, $I_P=I_{P_MAX}$	-3.0		3.0	%
Linearity Error	LIN_{ERR}	$T_A=-40^\circ C \sim 125^\circ C$		0.2	0.4	%

CC6924SG-3FB100 ($V_{CC}=3.3V$, $C_{OUT}=1nF$, $C_{REF}=1nF$, $T_A=25^\circ C$, unless otherwise specified)



Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Current Accuracy Range	I_P	-	-100		100	A
Sensitivity	Sens	full range of I_P		13.2		mV/A
Zero Current Differential Output Error	V_{OE}	$V_{OE}=V_{OUT}-V_{REF}$, $I_P=0A$	-5		5	mV
Noise	$V_{N(RMS)}$	$I_P=0A$		3		mV
Zero Current Output Offset Drift	ΔV_{OE}	$T_A=-40^\circ C \sim 125^\circ C$ V_{OE} offset voltage drift = $V_{OE_TA} - V_{OE_25^\circ C}$	-20		20	mV
Zero Current Quiescent Output Voltage Temperature Drift	$\Delta V_{OUT(Q)}$	$T_A=-40^\circ C \sim 125^\circ C$ $V_{OUT(Q)}$ voltage drift = $V_{OUT(Q)_TA} - V_{OUT(Q)_25^\circ C}$	-25		25	mV
Sensitivity Error	Δ_{SENS}	$T_A=-40^\circ C \sim 125^\circ C$	-2.5		2.5	%
Total Output Error	E_{TOT}	$T_A=-40^\circ C \sim 125^\circ C$, $I_P=I_{P_MAX}$	-3.0		3.0	%
Linearity Error	LIN_{ERR}	$T_A=-40^\circ C \sim 125^\circ C$		0.2	0.4	%





CC6924SG-3FB125 ($V_{CC}=3.3V$, $C_{OUT}=1nF$, $C_{REF}=1nF$, $T_A=25^\circ C$, unless otherwise specified)

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Current Accuracy Range	I_P	-	-125		125	A
Sensitivity	Sens	full range of I_P		10.56		mV/A
Zero Current Differential Output Error	V_{OE}	$V_{OE}=V_{OUT}-V_{REF}$, $I_P=0A$	-5		5	mV
Noise	$V_{N(RMS)}$	$I_P=0A$		2.5		mV
Zero Current Output Offset Drift	ΔV_{OE}	$T_A=-40^\circ C \sim 125^\circ C$ V_{OE} offset voltage drift = $V_{OE_TA} - V_{OE_25^\circ C}$	-20		20	mV
Zero Current Quiescent Output Voltage Temperature Drift	$\Delta V_{OUT(Q)}$	$T_A=-40^\circ C \sim 125^\circ C$ $V_{OUT(Q)}$ voltage drift = $V_{OUT(Q)_TA} - V_{OUT(Q)_25^\circ C}$	-25		25	mV
Sensitivity Error	Δ_{SENS}	$T_A=-40^\circ C \sim 125^\circ C$	-2.5		2.5	%
Total Output Error	E_{TOT}	$T_A=-40^\circ C \sim 125^\circ C$, $I_P=I_{P_MAX}$	-3.0		3.0	%
Linearity Error	LIN_{ERR}	$T_A=-40^\circ C \sim 125^\circ C$		0.2	0.4	%





CC6924SG-3FB150 ($V_{CC}=3.3V$, $C_{OUT}=1nF$, $C_{REF}=1nF$, $T_A=25^\circ C$, unless otherwise specified)

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Current Accuracy Range	I_P	-	-150		150	A
Sensitivity	Sens	full range of I_P		8.8		mV/A
Zero Current Differential Output Error	V_{OE}	$V_{OE}=V_{OUT}-V_{REF}$, $I_P=0A$	-5		5	mV
Noise	$V_{N(RMS)}$	$I_P=0A$		2		mV
Zero Current Output Offset Drift	ΔV_{OE}	$T_A=-40^\circ C \sim 125^\circ C$ V_{OE} offset voltage drift = $V_{OE_TA} - V_{OE_25^\circ C}$	-20		20	mV
Zero Current Quiescent Output Voltage Temperature Drift	$\Delta V_{OUT(Q)}$	$T_A=-40^\circ C \sim 125^\circ C$ $V_{OUT(Q)}$ voltage drift = $V_{OUT(Q)_TA} - V_{OUT(Q)_25^\circ C}$	-25		25	mV
Sensitivity Error	Δ_{SENS}	$T_A=-40^\circ C \sim 125^\circ C$	-2.5		2.5	%
Total Output Error	E_{TOT}	$T_A=-40^\circ C \sim 125^\circ C$, $I_P=I_{P_MAX}$	-3.0		3.0	%
Linearity Error	LIN_{ERR}	$T_A=-40^\circ C \sim 125^\circ C$		0.2	0.4	%





CURVE & WAVEFORM

 V_{OUT} positive step response waveform

 V_{OUT} negative step response waveform

CC6924SG-5FB020^[1]

 $\Delta V_{OUT(Q)}$ vs. T_A

 ΔV_{REF} vs. T_A

 ΔV_{OE} vs. T_A

 $\Delta Sens$ vs. T_A





[1] Green represents the average, Red represents the average+3Sigma, Blue represents the average-3Sigma(-40°C, 25°C, 85°C, 125°C)

CC6924SG-5FB030^[1]

 Δ V_{OUT(Q)} vs. T_A

 Δ V_{REF} vs. T_A

 Δ V_{OE} vs. T_A

 Δ Sens vs. T_A





[1] Green represents the average, Red represents the average+3Sigma, Blue represents the average-3Sigma(-40°C, 25°C, 85°C, 125°C)

CC6924SG-5FB040^[1]

 $\Delta V_{OUT(Q)} \text{ vs. } T_A$

 $\Delta V_{REF} \text{ vs. } T_A$

 $\Delta V_{OE} \text{ vs. } T_A$

 $\Delta Sens \text{ vs. } T_A$





[1] Green represents the average, Red represents the average+3Sigma, Blue represents the average-3Sigma(-40°C, 25°C, 85°C, 125°C)

CC6924SG-5FB050^[1]

 Δ V_{OUT(Q)} vs. T_A

 Δ V_{REF} vs. T_A

 Δ V_{OE} vs. T_A

 Δ Sens vs. T_A





[1] Green represents the average, Red represents the average+3Sigma, Blue represents the average-3Sigma(-40°C, 25°C, 85°C, 125°C)

CC6924SG-5FB065^[1]

 $\Delta V_{OUT(Q)} \text{ vs. } T_A$

 $\Delta V_{REF} \text{ vs. } T_A$

 $\Delta V_{OE} \text{ vs. } T_A$

 $\Delta Sens \text{ vs. } T_A$





[1] Green represents the average, Red represents the average+3Sigma, Blue represents the average-3Sigma(-40°C, 25°C, 85°C, 125°C)

CC6924SG-5FB075^[1]

 $\Delta V_{OUT(Q)} \text{ vs. } T_A$

 $\Delta V_{REF} \text{ vs. } T_A$

 $\Delta V_{OE} \text{ vs. } T_A$

 $\Delta Sens \text{ vs. } T_A$





[1] Green represents the average, Red represents the average+3Sigma, Blue represents the average-3Sigma(-40°C, 25°C, 85°C, 125°C)

CC6924SG-5FB080^[1]

 $\Delta V_{OUT(Q)} \text{ vs. } T_A$

 $\Delta V_{REF} \text{ vs. } T_A$

 $\Delta V_{OE} \text{ vs. } T_A$

 $\Delta Sens \text{ vs. } T_A$





[1] Green represents the average, Red represents the average+3Sigma, Blue represents the average-3Sigma(-40°C, 25°C, 85°C, 125°C)

CC6924SG-5FB100^[1]

 $\Delta V_{OUT(Q)} \text{ vs. } T_A$

 $\Delta V_{REF} \text{ vs. } T_A$

 $\Delta V_{OE} \text{ vs. } T_A$

 $\Delta Sens \text{ vs. } T_A$





[1] Green represents the average, Red represents the average+3Sigma, Blue represents the average-3Sigma(-40°C, 25°C, 85°C, 125°C)

CC6924SG-5FB125^[1]

 $\Delta V_{OUT(Q)}$ vs. T_A

 ΔV_{REF} vs. T_A

 ΔV_{OE} vs. T_A

 $\Delta Sens$ vs. T_A





[1] Green represents the average, Red represents the average+3Sigma, Blue represents the average-3Sigma(-40°C, 25°C, 85°C, 125°C)

CC6924SG-5FB150^[1]

 $\Delta V_{OUT(Q)} \text{ vs. } T_A$

 $\Delta V_{REF} \text{ vs. } T_A$

 $\Delta V_{OE} \text{ vs. } T_A$

 $\Delta Sens \text{ vs. } T_A$





[1] Green represents the average, Red represents the average+3Sigma, Blue represents the average-3Sigma(-40°C, 25°C, 85°C, 125°C)

CC6924SG-5FB200^[1]

 $\Delta V_{OUT(Q)}$ vs. T_A

 ΔV_{REF} vs. T_A

 ΔV_{OE} vs. T_A

 $\Delta Sens$ vs. T_A





[1] Green represents the average, Red represents the average+3Sigma, Blue represents the average-3Sigma(-40°C, 25°C, 85°C, 125°C)

CC6924SG-3FB020^[1]

 ΔV_{OUT(α)} vs. T_A

 ΔV_{REF} vs. T_A

 ΔV_{OE} vs. T_A

 ΔSens vs. T_A


[1] Green represents the average, Red represents the average+3Sigma, Blue represents the average-3Sigma(-40°C, 25°C, 85°C, 125°C)

CC6924SG-3FB030^[1]

 ΔV_{OUT(Q)} vs. T_A

 ΔV_{REF} vs. T_A

 ΔV_{OE} vs. T_A

 ΔSens vs. T_A


[1] Green represents the average, Red represents the average+3Sigma, Blue represents the average-3Sigma(-40°C, 25°C, 85°C, 125°C)

CC6924SG-3FB040^[1]

 Δ V_{OUT(Q)} vs. T_A

 Δ V_{REF} vs. T_A

 Δ V_{OE} vs. T_A

 Δ Sens vs. T_A


[1] Green represents the average, Red represents the average+3Sigma, Blue represents the average-3Sigma(-40°C, 25°C, 85°C, 125°C)

CC6924SG-3FB050^[1]



\Delta V_{OUT(Q)} vs. T_A



\Delta V_{REF} vs. T_A







\Delta V_{OE} vs. T_A







\Delta Sens vs. T_A





[1] Green represents the average, Red represents the average+3Sigma, Blue represents the average-3Sigma(-40°C, 25°C, 85°C, 125°C)

CC6924SG-3FB065^[1]

 $\Delta V_{OUT(Q)} \text{ vs. } T_A$

 $\Delta V_{REF} \text{ vs. } T_A$

 $\Delta V_{OE} \text{ vs. } T_A$

 $\Delta Sens \text{ vs. } T_A$


[1] Green represents the average, Red represents the average+3Sigma, Blue represents the average-3Sigma(-40°C, 25°C, 85°C, 125°C)

CC6924SG-3FB075^[1]

 $\Delta V_{OUT(Q)} \text{ vs. } T_A$

 $\Delta V_{REF} \text{ vs. } T_A$

 $\Delta V_{OE} \text{ vs. } T_A$

 $\Delta Sens \text{ vs. } T_A$


[1] Green represents the average, Red represents the average+3Sigma, Blue represents the average-3Sigma(-40°C, 25°C, 85°C, 125°C)

CC6924SG-3FB100^[1]

 Δ V_{OUT(Q)} vs. T_A

 Δ V_{REF} vs. T_A

 Δ V_{OE} vs. T_A

 Δ Sens vs. T_A


[1] Green represents the average, Red represents the average+3Sigma, Blue represents the average-3Sigma(-40°C, 25°C, 85°C, 125°C)

CC6924SG-3FB125^[1]



\Delta V_{OUT(Q)} vs. T_A



\Delta V_{REF} vs. T_A







\Delta V_{OE} vs. T_A



\Delta Sens vs. T_A

[1] Green represents the average, Red represents the average+3Sigma, Blue represents the average-3Sigma(-40°C, 25°C, 85°C, 125°C)

CC6924SG-3FB150^[1]

 Δ V_{OUT(Q)} vs. T_A

 Δ V_{REF} vs. T_A

 Δ V_{OE} vs. T_A

 Δ Sens vs. T_A

[1] Green represents the average, Red represents the average+3Sigma, Blue represents the average-3Sigma(-40°C, 25°C, 85°C, 125°C)

FUNCTION DESCRIPTION

The CC6924 device is a precision current sensor based on Hall sensor. It has less than 3% full scale error and zero current reference signal output in the whole temperature range, which can realize unidirectional or bidirectional current detection. The input current flows through a wire between isolated input current pins, which has a resistance of $0.3\text{m}\Omega$ at room temperature to reduce insertion loss. The magnetic field generated by the input current is sensed by Hall sensor and amplified by precise signal chain. It can be used for AC and DC current measurement with a bandwidth of 250kHz. The measuring current is 20-200A. There are 11 kinds of Current sensing range to choose. CC6924 is optimized for high accuracy and temperature stability, compensating for misalignment and sensitivity over the entire range.

The input current of CC6924 flows through the primary side of the package through IP+ and IP- pins, the current flowing through the chip generates a magnetic field proportional to the input current and is measured by an isolated Precision Hall sensor IC. Compared with other current measurement methods, the low impedance lead frame path reduces power consumption and does not require any external devices on the primary side. In addition, the internal integrated differential common mode suppression circuit can make the chip output not affected by external interference magnetic signal, and only measure the magnetic field generated by the input current, so as to suppress the interference of external magnetic field.

The typical resistance of the primary current input conductor at 25°C is $0.3\text{m}\Omega$. The lead frame is made of copper. The temperature coefficient of the input wire is positive, and the wire resistance increases with the increase of temperature. The typical temperature coefficient is 3900 ppm/ $^\circ\text{C}$. For every 100°C increase in temperature, the primary side resistance will increase by 39%.

INPUT CURRENT

In use, the primary side of the chip (package pins 1-8) is connected in series at any position in the whole circuit. The input current flowing from IP+ (package pins 1-4) to IP- (package pins 5-8) is positive, otherwise it is negative. Do not shunt resistors between IP+ and IP-, unless there are very special reasons - such as minimizing insertion loss - which will reduce the current flowing through the chip, and the wire resistance will also be affected by temperature drift, which requires external temperature and precision correction of the whole system.

VREF INPUT/OUTPUT CHARACTERISTIC

The quiescent output voltage V_{OQ} of V_{OUT} is VREF as a reference, VREF has two modes: input / output, which can be used as an internal reference to an external circuit or to adjust the V_{OQ} .


1. When using the VREF output mode:

Rated working voltage $V_{CC} = 5\text{V}$ series products, V_{REF} can reach 2.500 V, after factory programming, the nominal value error $\leq 5\text{mV}$;

The typical value of $I_{VREF_SOURCE} = 2.8\text{mA}$ and $I_{VREF_SINK} = 6\text{mA}$. Upon application, the current of 2mA of the V_{REF} is recommended.

2. When using the VREF input mode:

When the drive capability of the external reference exceeds the output of the reference op amp, the external reference forces V_{OQ} to use the external reference as a reference. When the input voltage is lower than the nominal value of V_{REF} , the drive capability of the input source needs to be higher than I_{VREF_SOURCE} ; When the input voltage is higher than the nominal value of V_{REF} , the drive capability of the input source needs to be higher than I_{VREF_SINK} . It is recommended that customers use an external reference source that $\pm 10\text{mA}$ drive capability for input. Limited by the rail-to-rail output range of the output op amp, the voltage range of the external input of V_{REF} is $0.1 \times V_{CC} \sim 0.9 \times V_{CC}$, V_{OQ} changes with V_{REF} , and the sensitivity of CC6924 remains unchanged.



VOUT OUTPUT CHARACTERISTIC

The quiescent output point of the CC6924 ($I_P = 0A$, with VREF in output mode) is 2.5V/1.65V.

When the current increases, the V_{OUT} increases until the saturation voltage of the output operational amplifier (VCC – rail voltage); when the current decreases, the V_{OUT} decreases until the saturation voltage (GND + rail voltage) of the Output Op Amp. Crosschip ensures the accuracy and linearity of V_{OUT} in the range of 0.5~4.5V/0.33~2.97V. In order to ensure the consistency of mass manufacturing, there is a certain margin in this range, but it is not recommended for customers to use this margin.

When the input current exceeds the range, the output of V_{OUT} is close to the rail voltage of the power supply. When the input current does not exceed the tolerance limit of the chip, the voltage will always be maintained. After the input current returns to the range, the output of V_{OUT} will return to normal without any damage to the chip.

When using the VREF output mode:

Product Name	Input Current	Nominal Supply Voltage(V)	Sensitivity(mV/A)	Calculation Formula (Note 1)
CC6924SG-5FB020	-20A ~ +20A	5	100	$V_{OUT} = 2500 + I_P(A) \times 100 \dots \text{(mV)}$
CC6924SG-5FB030	-30A ~ +30A	5	66.67	$V_{OUT} = 2500 + I_P(A) \times 66.67 \dots \text{(mV)}$
CC6924SG-5FB040	-40A ~ +40A	5	50	$V_{OUT} = 2500 + I_P(A) \times 50 \dots \text{(mV)}$
CC6924SG-5FB050	-50A ~ +50A	5	40	$V_{OUT} = 2500 + I_P(A) \times 40 \dots \text{(mV)}$
CC6924SG-5FB065	-65A ~ +65A	5	30.77	$V_{OUT} = 2500 + I_P(A) \times 30.77 \dots \text{(mV)}$
CC6924SG-5FB075	-75A ~ +75A	5	26.67	$V_{OUT} = 2500 + I_P(A) \times 26.67 \dots \text{(mV)}$
CC6924SG-5FB080	-80A ~ +80A	5	25	$V_{OUT} = 2500 + I_P(A) \times 25 \dots \text{(mV)}$
CC6924SG-5FB100	-100A ~ +100A	5	20	$V_{OUT} = 2500 + I_P(A) \times 20 \dots \text{(mV)}$
CC6924SG-5FB125	-125A ~ +125A	5	16	$V_{OUT} = 2500 + I_P(A) \times 16 \dots \text{(mV)}$
CC6924SG-5FB150	-150A ~ +150A	5	13.33	$V_{OUT} = 2500 + I_P(A) \times 13.33 \dots \text{(mV)}$
CC6924SG-5FB200	-200A ~ +200A	5	10	$V_{OUT} = 2500 + I_P(A) \times 10 \dots \text{(mV)}$
CC6924SG-3FB020	-20A ~ +20A	3.3	66	$V_{OUT} = 1650 + I_P(A) \times 66 \dots \text{(mV)}$
CC6924SG-3FB030	-30A ~ +30A	3.3	44	$V_{OUT} = 1650 + I_P(A) \times 44 \dots \text{(mV)}$
CC6924SG-3FB040	-40A ~ +40A	3.3	33	$V_{OUT} = 1650 + I_P(A) \times 33 \dots \text{(mV)}$
CC6924SG-3FB050	-50A ~ +50A	3.3	26.4	$V_{OUT} = 1650 + I_P(A) \times 26.4 \dots \text{(mV)}$

Continued:

CC6924SG-3FB065	-65A ~ +65A	3.3	20.31	$V_{OUT} = 1650 + I_P(A) \times 20.31 \dots \text{(mV)}$
CC6924SG-3FB075	-75A ~ +75A	3.3	17.6	$V_{OUT} = 1650 + I_P(A) \times 17.6 \dots \text{(mV)}$
CC6924SG-3FB100	-100A ~ +100A	3.3	13.2	$V_{OUT} = 1650 + I_P(A) \times 13.2 \dots \text{(mV)}$
CC6924SG-3FB125	-125A ~ +125A	3.3	10.56	$V_{OUT} = 1650 + I_P(A) \times 10.56 \dots \text{(mV)}$
CC6924SG-3FB150	-150A ~ +150A	3.3	8.8	$V_{OUT} = 1650 + I_P(A) \times 8.8 \dots \text{(mV)}$


When using the VREF input mode: ($0.1 \times V_{CC} \leq V_{REF} \leq 0.9 \times V_{CC}$)

Product Name	Input Current	Nominal Supply Voltage(V)	Sensitivity(mV/A)	Calculation Formula (Note 1)
CC6924SG-5FB020	-20A ~ +20A	5	100	$V_{OUT} = V_{REF} + I_P(A) \times 100 \dots \text{(mV)}$
CC6924SG-5FB030	-30A ~ +30A	5	66.67	$V_{OUT} = V_{REF} + I_P(A) \times 66.67 \dots \text{(mV)}$
CC6924SG-5FB040	-40A ~ +40A	5	50	$V_{OUT} = V_{REF} + I_P(A) \times 50 \dots \text{(mV)}$
CC6924SG-5FB050	-50A ~ +50A	5	40	$V_{OUT} = V_{REF} + I_P(A) \times 40 \dots \text{(mV)}$
CC6924SG-5FB065	-65A ~ +65A	5	30.77	$V_{OUT} = V_{REF} + I_P(A) \times 30.77 \dots \text{(mV)}$
CC6924SG-5FB075	-75A ~ +75A	5	26.67	$V_{OUT} = V_{REF} + I_P(A) \times 26.67 \dots \text{(mV)}$
CC6924SG-5FB080	-80A ~ +80A	5	25	$V_{OUT} = V_{REF} + I_P(A) \times 25 \dots \text{(mV)}$
CC6924SG-5FB100	-100A ~ +100A	5	20	$V_{OUT} = V_{REF} + I_P(A) \times 20 \dots \text{(mV)}$
CC6924SG-5FB125	-125A ~ +125A	5	16	$V_{OUT} = V_{REF} + I_P(A) \times 16 \dots \text{(mV)}$
CC6924SG-5FB150	-150A ~ +150A	5	13.33	$V_{OUT} = V_{REF} + I_P(A) \times 13.33 \dots \text{(mV)}$
CC6924SG-5FB200	-200A ~ +200A	5	10	$V_{OUT} = V_{REF} + I_P(A) \times 10 \dots \text{(mV)}$
CC6924SG-3FB020	-20A ~ +20A	3.3	66	$V_{OUT} = V_{REF} + I_P(A) \times 66 \dots \text{(mV)}$
CC6924SG-3FB030	-30A ~ +30A	3.3	44	$V_{OUT} = V_{REF} + I_P(A) \times 44 \dots \text{(mV)}$
CC6924SG-3FB040	-40A ~ +40A	3.3	33	$V_{OUT} = V_{REF} + I_P(A) \times 33 \dots \text{(mV)}$
CC6924SG-3FB050	-50A ~ +50A	3.3	26.4	$V_{OUT} = V_{REF} + I_P(A) \times 26.4 \dots \text{(mV)}$
CC6924SG-3FB065	-65A ~ +65A	3.3	20.31	$V_{OUT} = V_{REF} + I_P(A) \times 20.31 \dots \text{(mV)}$
CC6924SG-3FB075	-75A ~ +75A	3.3	17.6	$V_{OUT} = V_{REF} + I_P(A) \times 17.6 \dots \text{(mV)}$
CC6924SG-3FB100	-100A ~ +100A	3.3	13.2	$V_{OUT} = V_{REF} + I_P(A) \times 13.2 \dots \text{(mV)}$
CC6924SG-3FB125	-125A ~ +125A	3.3	10.56	$V_{OUT} = V_{REF} + I_P(A) \times 10.56 \dots \text{(mV)}$
CC6924SG-3FB150	-150A ~ +150A	3.3	8.8	$V_{OUT} = V_{REF} + I_P(A) \times 8.8 \dots \text{(mV)}$

Note1:This formula is only applicable to DC current calculations, when AC current applications, one should pay attention to $I_{PEAK}=1.414 \times I_{RMS}$ and pay attention to the positive and negative current direction.


OFFSET VOLTAGE

Offset Voltage, or V_{OE} , is defined as the difference between $V_{OUT(Q)}$ and V_{REF} (as shown in the figure below). V_{OE} includes the drift of $V_{OUT(Q)}$ minus V_{REF} from room to hot or room to cold (-40°C to $+125^{\circ}\text{C}$ respectively).


**OUTPUT VOLTAGE OPERATING RANGE**

As shown in the figure, the output voltage operating range V_{OOR} is the swing range of the linear output of V_{OUT} . V_{OUT} beyond V_{OOR} could still work until V_{SAT} , but performance deteriorated in this range.


Voltage Output Operating Range for V_{cc} and Output Modes	
V_{cc}	Bidirectional
5V	± 2



TYPICAL APPLICATION CIRCUITS




Recommended Typical Applications




Signal Attenuation Circuitry


Note: It is recommended to use CC6924SG-3, 3.3V voltage power supply



Over-current Fault Detector



Zero Migration Application (VREF Output Mode)



Zero Migration Application (VREF Input Mode)


TEMPERATURE RISE vs. INPUT CURRENT

When designing any current sensing system, self-heating due to a single current measurement should be considered. As current flows through the system, the sensor, printed circuit board (PCB), and contact resistance all generate heat. Temperature rise is highly dependent on PCB layout, copper foil thickness, cooling method, and input current method. The primary current includes peak current, the conducting time of current and duty cycle. The data presented in this section is a DC test that can be used to approximate the temperature rise of AC and pulse currents.


The test environment of this experiment is: room temperature, open environment, no wind; The temperature rise test method is: the chip surface is attached to our Demo Board, and the temperature data is collected after the chip temperature is stable. The following chart shows the CC6924 package body surface temperature vs. the continuous current flowing through the primary side.

The heat capacity of the CC6924 should be verified by final customer under the specific conditions of the application. The maximum junction temperature $T_{J(MAX)}$ (165°C) should not be exceeded.

For further information on testing this application, please refer to Crosschip 《Crosschip Current Sensor Layout Application Guide》 .

Relationship between Package Temperature & Input Current



Input Current (IP) vs. Package Temperature




I_CON vs T_A

Note: Based on the demo board test, for specific applications, it is necessary to strengthen heat dissipation or choose T_g high plates according to actual application scenarios.

Continuous power supply at 150A current, if the wind speed of the auxiliary cooling fan is 14.5 m/s, the temperature rise can be controlled within the 5°C range.




Package Thermography
(Input Current 50A)




Package Thermography
(Input Current 60A)

Thickness 1.6mm, FR-4 double panel, top 2 oz and inner 0.5 oz copper foil, total 800mm², Connected with the IP pin, and each layer of copper foil connected with holes

Test environment: open environment, quiescent air




Package Thermography
(Input Current 70A)



Package Thermography
(Input Current 80A)

PACKAGE INFORMATION

SOP16W Package



Size	Millimeters		
	Min.	Typ.	Max.
A	2.35	-	2.65
A1	0.10	-	0.30
b	0.33	-	0.51
c	0.23	-	0.32
D	10.10	-	10.50
E1	7.40	-	7.60
E	10.00	-	10.63
e	1.27 BSC		
L	0.40	-	1.27
h	0.25	-	0.75
θ	0°	-	8°

Marking:

1st Line: CC6924SG – Device Name2nd Line: XYZMMM


- X – Rated operating voltage
 - Y – Output type
 - Z – Output polarity
 - MMM – the current range
- 3rd Line: XXXXXXXX
- XXXXXXXX – Production serial number

Note:



1. All dimensions are in millimeters.

2. For details: refer to Product Name Definition

PACKAGE REFERENCE



shorten pad length and increase creepage distance


TAPE AND REEL INFORMATION
Reel Dimensions

QUADRANT ASSIGNMENTS FOR PIN1 ORIENTATION IN TAPE


Reel Basic Size(mm)					
A	B	W1	W2 Max	T	D
330	100	16.4	22.4	1.5	270
Carrier Tape Basic Size(mm)					
W	A0	B0	K0	P0	P1
16±0.30	10.7±0.1	10.7±0.1	3.00±0.1	4.0±0.1	12.00±0.1
P2	F	S	E	D0	T
2.0±0.1	7.5±0.1	0.0±0.1	1.75±0.1	1.5^{+0.1}_{-0.0}	0.3±0.05

Note: Tolerance ± 0.2mm is not specified.

THE WELDING PROCESS OF THE CHIP

Welding Process Requirements:



REVISION HISTORY

Revision Date	Description of Revision	Revision
2023.09	Add 80A range-related information; Add the ETOT test conditions.	rev1.3
2023.12	Refresh temperature drift curves for all ranges; Supplementary Typical Application Diagram - Zero Migration Application (Reference Output Mode).	rev1.4
2024.03	Add <i>CTI</i> parameter information; Changed the description of <i>Total Output Error</i> to <i>Sensitivity Temperature Drift</i> in Characteristics.	rev1.5
2024.04	<i>ESD (CDM)</i> parameter indicator updated from "1kV" to "2kV".	rev1.6
2024.05	Add 80A range-related information.	rev1.7

CrossChip

CrossChip Microsystems Inc. was founded in 2013, is a national high-tech enterprise, engaged in integrated circuit design and sales. The company has strong technical strength, has more than 60 kinds of patents, mainly used in Hall sensor signal processing, with the following product lines:

- ✓ High precision linear Hall sensor
- ✓ All kinds of Hall switches
- ✓ Single phase motor drive
- ✓ Single chip current sensor
- ✓ AMR Magnetoresistance sensor
- ✓ Isolation drive class chip

Contact us

Chengdu

Address: 4th floor, unit 2, building 3, No. 88, Tianchen Road, Gaoxinxi Zone, Chengdu, Sichuan Province
Tel: + 86 - 028 - 87787685
Email: support@crosschipmicro.com
Website: <https://www.crosschipmicro.com>

Shenzhen

Address: 605 room, 6F, Beike building, NO.18 Keyuan Rd, Yuehai Street, Nanshan District, Shenzhen

Shanghai

Address: Room 602, Building 1, Shengda Tiandi Yuanchuanggu, No. 88, Shengrong Road, Pudong New District, Shanghai

Suzhou

Address: NO.78 Jinshan Rd East, Suzhou High-tech Zone, Huqiu District, Suzhou City, Jiangsu Province